

# SS34FA-S310FA

## Schottky Barrier Rectifiers, Surface Mount, 3 A, 40 V-100 V

### Features

- Low Power Loss, High Efficiency
- Guard Ring for Overvoltage Protection
- High Surge Current Capability
- UL Flammability 94V-0 Classification
- MSL 1 per J-STD-020
- NRVB Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- This Device is Pb-Free and RoHS Compliant

### ABSOLUTE MAXIMUM RATINGS

(Values are at  $T_A = 25^\circ\text{C}$  unless otherwise noted)

| Symbol      | Parameter   | SS34FA      | SS36FA      | S310FA | Unit             |
|-------------|---|-------------|-------------|--------|------------------|
| $V_{RRM}$   | Repetitive Peak Reverse Voltage   | 40          | 60          | 100    | V                |
| $V_{RMS}$   | RMS Reverse Voltage   | 28          | 42          | 70     | V                |
| $V_R$       | DC Blocking Voltage   | 40          | 60          | 100    | V                |
| $I_{F(AV)}$ | Average Forward Rectified Current   | 3           |             |        | A                |
| $I_{FSM}$   | Peak Forward Surge Current: 8.3 ms Single Half Sine-Wave Superimposed on Rated Load | 80          |             |        | A                |
| $T_J$       | Operating Junction Temperature Range  | -55 to +125 | -55 to +150 |        | $^\circ\text{C}$ |
| $T_{STG}$   | Storage Temperature Range   | -55 to +150 |             |        | $^\circ\text{C}$ |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

### THERMAL CHARACTERISTICS

(Values are at  $T_A = 25^\circ\text{C}$  unless otherwise noted) (Note 1)


| Symbol          | Parameter                                 | Value | Unit                      |
|-----------------|---|-------|---------------------------|
| $\psi_{JL}$     | Thermal Characteristics, Junction-to-Lead | 16    | $^\circ\text{C}/\text{W}$ |
| $R_{\theta JA}$ | Thermal Resistance, Junction-to-Ambient   | 152   | $^\circ\text{C}/\text{W}$ |

1. Per JESD51-3 Recommended Thermal Test Board. Device mounted on FR-4 PCB, board size = 76.2 mm  $\times$  114.3 mm.




ON Semiconductor®


[www.onsemi.com](http://www.onsemi.com)



SOD-123FL  
CASE 425AB



### MARKING DIAGRAM



&Y = Binary Calendar Year Coding Scheme  
&Z = Assembly Plant Code  
\* = Specific Device Code (34L, 36L or 30L)  
&G = Single Digit Weekly Datecode

### ORDERING INFORMATION

See detailed ordering and shipping information on page 2 of this data sheet.

## SS34FA–S310FA

### ELECTRICAL CHARACTERISTICS (Values are at $T_A = 25^\circ\text{C}$ unless otherwise noted)

| Symbol   | Parameter                                      | Conditions   | SS34FA | SS36FA | S310FA | Unit |
|----------|--|--|--------|--------|--------|------|
| $V_F$    | Maximum Instantaneous Forward Voltage (Note 2) | $I_F = 3\text{ A}$   | 0.50   | 0.75   | 0.85   | V    |
| $I_R$    | Maximum Reverse Current at Rated $V_R$         | $T_J = 25^\circ\text{C}$   | 0.5    |        | 0.1    | mA   |
|          |  | $T_J = 125^\circ\text{C}$  | 60     | 10     | 5      |      |
| $C_J$    | Typical Junction Capacitance                   | $V_R = 4\text{ V}$ , $f = 1\text{ MHz}$                              | 152    | 117    | 78     | pF   |
| $T_{rr}$ | Typical Reverse Recovery Time                  | $I_F = 0.5\text{ A}$ , $I_R = 1\text{ A}$ , $I_{RR} = 0.25\text{ A}$ | 12     | 11     | 8      | ns   |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

2. Pulse test with  $PW = 300\ \mu\text{s}$ , 1% duty cycle.

### ORDERING INFORMATION

| Part Number         | Top Mark | Package                | Shipping <sup>†</sup> |
|---------------------|----------|------------------------|-----------------------|
| SS34FA, NRVBSS34FA* | 34L      | SOD-123FL<br>(Pb-Free) | 3,000 / Tape & Reel   |
| SS36FA, NRVBSS36FA* | 36L      | SOD-123FL<br>(Pb-Free) | 3,000 / Tape & Reel   |
| S310FA, NRVBS310FA* | 30L      | SOD-123FL<br>(Pb-Free) | 3,000 / Tape & Reel   |

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

\*NRVB Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable

# SS34FA-S310FA

## TYPICAL PERFORMANCE CHARACTERISTICS




Figure 1. Forward Current Derating Curve




Figure 2. Maximum Non-Repetitive Forward Surge Current




Figure 3. Typical Forward Characteristics




Figure 4. Typical Forward Characteristics




Figure 5. Typical Forward Characteristics




Figure 6. Typical Reverse Characteristics

# SS34FA-S310FA

## TYPICAL CHARACTERISTICS (Continued)




Figure 7. Typical Reverse Characteristics




Figure 8. Typical Reverse Characteristics






Figure 9. Typical Junction Capacitance

SOD-123FL  
CASE 425AB  
ISSUE O


DATE 31 AUG 2016




TOP VIEW



LAND PATTERN RECOMMENDATION



FRONT VIEW



BOTTOM VIEW

NOTES:

- A. NO INDUSTRY STANDARD APPLIES TO THIS PACKAGE.
- B. ALL DIMENSIONS ARE IN MILLIMETERS.
- C. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH AND TIE BAR PROTRUSIONS.

|                         |                    |   |
|-------------------------|--------------------|---|
| <b>DOCUMENT NUMBER:</b> | <b>98AON13722G</b> | Electronic versions are uncontrolled except when accessed directly from the Document Repository.<br>Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| <b>DESCRIPTION:</b>     | <b>SOD-123FL</b>   | <b>PAGE 1 OF 1</b>  |

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## PUBLICATION ORDERING INFORMATION

### LITERATURE FULFILLMENT:

Email Requests to: [orderlit@onsemi.com](mailto:orderlit@onsemi.com)

**onsemi Website:** [www.onsemi.com](http://www.onsemi.com)

### TECHNICAL SUPPORT

**North American Technical Support:**

Voice Mail: 1 800-282-9855 Toll Free USA/Canada

Phone: 011 421 33 790 2910

**Europe, Middle East and Africa Technical Support:**

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative