

Product Overview

LMV324: Operational Amplifier, Low Power, Rail to Rail Output, CMOS Op-Amp

For complete documentation, see the data sheet.

The LMV321, LMV358, and LMV324 are single, dual, and quad low voltage op-amps with rail-to-rail output swing. These amplifiers are a cost-effective solution for applications where low power consumption and space saving packages are critical. Specification tables are provided for operation from power supply voltages at 2.7 V and 5 V. Rail-to-Rail operation allows for optimal signal-to-noise applications. Ultra low quiescent current makes this series of amplifiers ideal for portable, battery operated equipment. The common mode input range includes ground making the device useful for low-side current-shunt measurements. The ultra small packages allow for placement on the PCB in close proximity to the signal source thereby reducing noise pickup.

Features

- Operation from 2.7 V to 5.0 V Single-Sided Power Supply
- No Output Crossover Distortion
- Industrial temperature Range: -40C to +85C
- Rail-to-Rail Output
- Low Quiescent Current
- No Output Phase-Reversal from Overdriven Input

Benefits

- Compatible with the most common operating conditions
- Guarantees signal integrity
- Robust thermal performance
- Reduces supply requirements
- Improves battery life and power consumption
- Predictable system behavior

Applications

- Voltage regulation
- Sensor amplification or buffering

End Products

- Notebook PC
- Hard disk drives
- Routers and switches
- Other portables

Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	Rail to Rail	Channels	V _S Min (V)	V _S Max (V)	I _q Typ (mA)	V _{OS} Max (mV)	GBW Typ (MHz)	SR Typ (V/μs)	I _O Typ (mA)	ΔV _O /ΔT (μV/°C)	e _N (nV/√Hz)	I _{bias} Typ (pA)	CMRR Typ (dB)	Architecture	Temperature Range (°C)	Package Type
LMV324DR2G	0.1555	Pb-free Halide free	Active	Output	4	2.5	5.5	0.065	9	1	1	160	5	50	<1000	65	CMOS	-40 to 85	SOIC-14
LMV324DTBR2G	0.1707	Pb-free Halide free	Active	Output	4	2.5	5.5	0.065	9	1	1	160	5	50	<1000	65	CMOS	-40 to 85	TSSOP-14

For more information please contact your local sales support at www.onsemi.com.

Created on: 8/3/2020