# onsemi

# **MOSFET** - Power, Single N-Channel

60 V, 5.3 mΩ, 89 A

# NVTYS005N06CL

#### Features

- Small Footprint (3.3 x 3.3 mm) for Compact Design
- Low R<sub>DS(on)</sub> to Minimize Conduction Losses
- Low Capacitance to Minimize Driver Losses
- AEC–Q101 Qualified and PPAP Capable
- These Devices are Pb-Free and are RoHS Compliant

#### **MAXIMUM RATINGS** (T<sub>J</sub> = $25^{\circ}$ C unless otherwise noted)

Parameter			Symbol	Value	Unit
Drain-to-Source Voltage			V <sub>DSS</sub>	60	V
Gate-to-Source Voltage	Gate-to-Source Voltage			±20	V
Continuous Drain		$T_C = 25^{\circ}C$	۱ <sub>D</sub>	89	А
Current $R_{\theta JC}$ (Notes 1, 2, 3, 4)	Steady	T <sub>C</sub> = 100°C		63	
Power Dissipation	State	T <sub>C</sub> = 25°C	PD	76	W
$R_{\theta JC}$ (Notes 1, 2, 3)		$T_C = 100^{\circ}C$		38	
Continuous Drain		$T_A = 25^{\circ}C$	۱ <sub>D</sub>	18	А
Current R <sub>θJA</sub> (Notes 1, 3, 4)	Steady	T <sub>A</sub> = 100°C		13	
Power Dissipation	State	T <sub>A</sub> = 25°C	PD	3.2	W
$R_{\theta JA}$ (Notes 1, 3)		T <sub>A</sub> = 100°C		1.6	
Pulsed Drain Current	T <sub>A</sub> = 25	°C, t <sub>p</sub> = 10 μs	I <sub>DM</sub>	430	А
Operating Junction and Storage Temperature Range			T <sub>J</sub> , T <sub>stg</sub>	–55 to +175	°C
Source Current (Body Diode)			۱ <sub>S</sub>	63	А
Single Pulse Drain-to-Source Avalanche Energy (I <sub>L(pk)</sub> = 4.9 A)			E <sub>AS</sub>	155	mJ
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)			ΤL	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.


#### THERMAL RESISTANCE MAXIMUM RATINGS (Note 1)

Parameter	Symbol	Value	Unit
Junction-to-Case - Steady State (Note 3)	$R_{\theta JC}$	2.0	°C/W
Junction-to-Ambient - Steady State (Note 3)	R <sub>0.IA</sub>	46.7	

- 1. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.
- Psi (Ψ) is used as required per JESD51–12 for packages in which substantially less than 100% of the heat flows to single case surface.
- 3. Surface-mounted on FR4 board using a 650 mm<sup>2</sup>, 2 oz. Cu pad.
- Continuous DC current rating. Maximum current for pulses as long as 1 second is higher but is dependent on pulse duration and duty cycle.

V <sub>(BR)DSS</sub>	R <sub>DS(on)</sub> MAX	I <sub>D</sub> MAX	
60 V	5.3 mΩ @ 10 V	89 A	
00 V	7.3 mΩ @ 4.5 V	09 A	

#### N-Channel





LFPAK8 3.3x3.3 CASE 760AD

#### MARKING DIAGRAM



005N06CL = Specific Device Code

A = Assembly Location

WL = Wafer Lot

= Year

Υ

W = Work Week

(Note: Microdot may be in either location)

## **ORDERING INFORMATION**


See detailed ordering, marking and shipping information in the package dimensions section on page 5 of this data sheet.

## ELECTRICAL CHARACTERISTICS (T<sub>J</sub> = 25°C unless otherwise noted)


Parameter	Symbol	Test Condition		Min	Тур	Max	Unit
OFF CHARACTERISTICS		•					
Drain-to-Source Breakdown Voltage	V <sub>(BR)DSS</sub>	$V_{GS}$ = 0 V, $I_D$ = 250 $\mu$ A		60			V
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	$V_{CS} = 0 V$ $T_J = 25^{\circ}C$				10	μA
			T <sub>J</sub> = 125°C			250	
Gate-to-Source Leakage Current	I <sub>GSS</sub>	V <sub>DS</sub> = 0 V, V <sub>G</sub>	<sub>iS</sub> = 20 V		1	100	nA
ON CHARACTERISTICS (Note 5)							
Gate Threshold Voltage	V <sub>GS(TH)</sub>	$V_{GS} = V_{DS}, I_{D}$	<sub>)</sub> = 75 μA	1.2		2.2	V
Drain-to-Source On Resistance	R <sub>DS(on)</sub>	V <sub>GS</sub> = 10 V, I	<sub>D</sub> = 50 A		4.4	5.3	mΩ
		V <sub>GS</sub> = 4.5 V, I	<sub>D</sub> = 50 A		6.1	7.3	
Forward Transconductance	9 <sub>FS</sub>	V <sub>DS</sub> = 5 V, I <sub>C</sub>	<sub>0</sub> = 50 A		100		S
CHARGES AND CAPACITANCES							
Input Capacitance	C <sub>iss</sub>				1890		pF
Output Capacitance	C <sub>oss</sub>	V <sub>GS</sub> = 0 V, f = V <sub>DS</sub> = 2	1.0 MHz, 5 V		1060		
Reverse Transfer Capacitance	C <sub>rss</sub>	v <sub>DS</sub> = 25 v			11		1
Total Gate Charge	Q <sub>G(TOT)</sub>				11.5		nC
Threshold Gate Charge	Q <sub>G(TH)</sub>	$V_{GS}$ = 4.5 V, $V_{DS}$ = 48 V, $I_{D}$ = 50 A			2.7		nC
Gate-to-Source Charge	Q <sub>GS</sub>				5.3		
Gate-to-Drain Charge	Q <sub>GD</sub>				2.9		
Total Gate Charge	Q <sub>G(TOT)</sub>	V <sub>GS</sub> = 10 V, V <sub>DS</sub> = -	48 V, I <sub>D</sub> = 50 A		25		nC
SWITCHING CHARACTERISTICS (No	te 6)						
Turn-On Delay Time	t <sub>d(on)</sub>				15		ns
Rise Time	t <sub>r</sub>	V <sub>GS</sub> = 4.5 V, Vr	ns = 48 V,		9		
Turn-Off Delay Time	t <sub>d(off)</sub>	V <sub>GS</sub> = 4.5 V, V <sub>I</sub> I <sub>D</sub> = 50 A, R <sub>G</sub>	= 2.5 Ω		19		
Fall Time	t <sub>f</sub>				8		
DRAIN-SOURCE DIODE CHARACTEF	ISTICS						
Forward Diode Voltage	V <sub>SD</sub>	V <sub>GS</sub> = 0 V,	$T_J = 25^{\circ}C$		0.9	1.2	V
		$I_{\rm S} = 50 \text{A}$ $T_{\rm J} = 125^{\circ}\text{C}$			0.8		
Reverse Recovery Time	t <sub>RR</sub>	V <sub>GS</sub> = 0 V, dI <sub>S</sub> /dt = 100 A/µs, I <sub>S</sub> = 50 A			43		ns
Charge Time	t <sub>a</sub>				14		
Discharge Time	t <sub>b</sub>				29		
Reverse Recovery Charge	Q <sub>RR</sub>				32		nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.
5. Pulse Test: Pulse Width ≤ 300 µs, Duty Cycle ≤ 2%.
6. Switching characteristics are independent of operating junction temperatures.

## **TYPICAL CHARACTERISTICS**



## **TYPICAL CHARACTERISTICS**



## **TYPICAL CHARACTERISTICS**




Figure 13. Thermal Characteristics


#### **DEVICE ORDERING INFORMATION**

Device	Marking	Package	Shipping <sup>†</sup>
NVTYS005N06CLTWG	005N 06CL	LFPAK33 (Pb–Free)	3000 / Tape & Reel


+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

#### PACKAGE DIMENSIONS


LFPAK8 3.3x3.3, 0.65P CASE 760AD ISSUE E



TOP VIEW




DETAIL 'A' SCALE: 2:1



LAND PATTERN RECOMMENDATION

\*FOR ADDITIONAL INFORMATION ON OUR PB-FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ON SEMICONDUCTOR SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERRM/D.

-		-c2
(	L L L	DETAIL "A"
c-		
SIC	DE VIEV	/



NOTES:

A2

- 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994
- 2. CONTROLLING DIMENSION: MILLIMETERS
- 3. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR BURRS. MOLD FLASH, PROTRUSIONS OR BURRS SHALL NOT EXCEED 0.150mm PER SIDE.
- 4. DIMENSIONS D AND E ARE DETERMINED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY.
- DATUMS A AND B ARE DETERMINED AT DATUM
- PLANE H 6
- OPTIONAL MOLD FEATURE.

	MILLIMETERS			
Billi	MIN.	NOM.	MAX.	
A	0.95	1.05	1.15	
A1	0.00	0.05	0.10	
A2	0.95	1.00	1.05	
A3		0.15 REI	F	
b	0.27	0.32	0.37	
с	0.12	0.17	0.22	
c2	0.12	0.17	0.22	
D1	2.50	2.60	2.70	
D2	1.82	1.92	2.02	
D3	1.46	1.56	1.66	
D4	0.20	0.25	0.30	
Е	3.20	3.30	3.40	
E1	3.00	3.10	3.20	
E2	2.15	2.25	2.35	
е	0.65 BSC			
Н	3.20	3.30	3.40	
L	0.25	0.37	0.50	
L1	0.48	0.58	0.68	
L2	0.35	0.45	0.55	
Q	0.45	0.50	0.55	
θ	0°	4°	8°	

onsemi. OnSemi, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries. LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and calcular performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that onsemi was negligent regarding the design or manufacture of the part. onsemi is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

#### TECHNICAL SUPPORT

Email Requests to: orderlit@onsemi.com

onsemi Website: www.onsemi.com

North American Technical Support: Voice Mail: 1 800–282–9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support: Phone: 00421 33 790 2910 For additional information, please contact your local Sales Representative