

Product Overview

MSR860: Power Rectifier, Soft Recovery, Switch-mode, 8 A, 600 V

For complete documentation, see the data sheet.

The Soft Recovery Rectifier is designed for use as free wheeling diodes in variable speed motor control applications and switching power supplies.

Features

- Soft Recovery with Guaranteed Low Reverse Recovery Charge (QRR) and Peak Reverse Recovery Current (IRRM)
- 150 C Operating Junction Temperature
- Epoxy meets UL94, VO @ 1/8"
- Low Forward Voltage
- Low Leakage Current
- Case: Molded Epoxy
- Weight: 1.9 Grams (approximately)
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads Readily Solderable
- Lead Temperature for Soldering Purposes: 260 C Max. for 10 Seconds

Applications

- SMPS: CCM PFC

End Products

- ATX Power Supply
- Flat Panel Display

Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	Type	$I_{O(rec)}$ Max (A)	t_r Max (ns)	V_{RRM} Max (V)	V_{FM} Max (V)	I_{FSM} Max (A)	I_R Max (mA)	Package Type
MSR860G	0.3841	Pb-free	Active	Ultrasoft	8	120	600	1.7	100	0.01	TO-220-2
MSRF860G	0.3467	Pb-free	Active	Ultrasoft	8	120	600	1.7	100	0.01	TO-220-2 FullPak

For more information please contact your local sales support at www.onsemi.com.

Created on: 8/11/2020