

Product Overview

MBRS140: Schottky Power Rectifier, Surface Mount, 1.0 A, 40 V

For complete documentation, see the data sheet.

The Schottky Rectifier employs the Schottky Barrier principle in a large area metal-to-silicon power diode. The Schottky Rectifier's state-of-the-art geometry features epitaxial construction with oxide passivation and metal overlay contact. It is ideally suited for low voltage, high frequency rectification, or as free wheeling and polarity protection diodes in surface mount applications where compact size and weight are critical to the system.

Features

- Small Compact Surface Mountable Package with J-Bend Leads
- Rectangular Package for Automated Handling
- Highly Stable Oxide Passivated Junction
- Very Low Forward Voltage Drop 5 Volts Max @ 1.0 A, T_J5°C)
- Excellent Ability to Withstand Reverse Avalanche Energy Transients
- Guardring for Stress Protection Mechanical Characteristics:
- Case: Epoxy, Molded
- Weight: 95 mg (approximately)
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable
- Lead and Mounting Surface Temperature for Soldering Purposes: 260°C Max. for 10 Seconds

For more features, see the data sheet

Part Electrical Specifications

Product	Compliance	Status	Configuration	V _{RRM} Min (V)	V _F Max (V)	I _{RM} Max (μA)	I _{O(rec)} Max (A)	I _{FSM} Max (A)	t _r Max (ns)	C _j Max (pF)	Package Type
MBRS140	Pb-free	Active	Single	40	0.6	1000	1	40	-	-	SMB
MBRS140T3G	Pb-free Halide free	Active	Single	40	0.6	1000	1	40	-	-	SMB-2
SBR8140T3G	AEC Qualified	Active	Single	40	0.6	1000	1	40	-	-	SMB-2
	PPAP Capable										
	Pb-free										
	Halide free										

For more information please contact your local sales support at www.onsemi.com.

Created on: 9/17/2019