

Product Overview

MBRS540: Schottky Power Rectifier, Surface Mount, 5.0 A, 40 V

For complete documentation, see the data sheet.

This Schottky Rectifier employs the Schottky Barrier principle in a large area metal-to-silicon power diode. State-of-the-art geometry features epitaxial construction with oxide passivation and metal overlay contact. The Schottky Rectifier is ideally suited for low voltage, high frequency rectification, or as free wheeling and polarity protection diodes in surface mount applications where compact size and weight are critical to the system.

Features

- Compact Surface Mountable Package with J-Bend leads
- Rectangular Package for Automated Handling
- Highly Stable Oxide Passivated Junction
- Excellent Ability to Withstand Reverse Avalanche Energy Transients
- Guardring for Stress Protection
- Cathode Lead Indicated by polarity Notch
- ESD Ratings, Machine Model = C, Human Body Model = 3B
- Device Meets MSL 1 Requirements
- Pb-Free Package is Available
- AEC-Q101 Qualified and PPAP Capable

For more features, see the data sheet

Applications

- ac/dc and dc-dc Converters
- Reverse Battery Protection

Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	Configuration	V_{RRM} Min (V)	V_F Max (V)	I_{RM} Max (μ A)	$I_{O(rec)Max}$ (A)	I_{FSM} Max (A)	t_{rr} Max (ns)	C_j Max (pF)	Package Type
MBRS540T3G	0.1896	Pb-free	Active	Single	40	0.5	300	5	190	-	-	SMC-2
		Halide free										
NRVBS540T3G	0.264	AEC Qualified PPAP Capable Pb-free Halide free	Active	Single	40	0.5	0.3	5	190	-	-	SMC-2

For more information please contact your local sales support at www.onsemi.com.

Created on: 12/6/2019