

Product Overview

MMBTA56L: PNP Bipolar Transistor

For complete documentation, see the data sheet.

The NPN Bipolar Transistor is designed for use in linear and switching applications. The device is housed in the SOT-23 package, which is designed for lower power surface mount applications.

Features

- Low $r_{DS(on)}$ Provides Higher Efficiency and Extends Battery Life
- Miniature SOT-23 Surface Mount Package Saves Board Space
- Pb-Free Packages are Available
- S and NSV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable

Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	Polarity	Type	$V_{CE(sat) Max}$ (V)	I_C Cont. (A)	$V_{CEO Min}$ (V)	V_{CBO} (V)	V_{EBO} (V)	$V_{BE(sat)}$ (V)	$V_{BE(on)}$ (V)	$h_{FE Min}$	$h_{FE Max}$	f_T Min (MHz)	$P_{TM Max}$ (W)	Package Type
MMBTA56LT1G	0.0249	Pb-free Halide free non AEC-Q and PPAP	Active	PNP	General Purpose	0.25	0.5	80	80	4	-	1.2	100	-	50	0.225	SOT-23-3
MMBTA56LT3G	0.0249	Pb-free Halide free non AEC-Q and PPAP	Active	PNP	General Purpose	0.25	0.5	80	80	4	-	1.2	100	-	50	0.225	SOT-23-3
SMMBTA56LT1G	0.0463	AEC Qualified PPAP Capable Pb-free Halide free	Active	PNP	General Purpose	0.25	0.5	80	80	4	-	1.2	100	-	50	0.225	SOT-23-3
SMMBTA56LT3G	0.0463	AEC Qualified PPAP Capable Pb-free Halide free	Active	PNP	General Purpose	0.25	0.5	80	80	4	-	1.2	100	-	50	0.225	SOT-23-3

For more information please contact your local sales support at www.onsemi.com.

Created on: 4/16/2021