

Product Overview

NSS12201L: Low VCE(sat) Transistor, NPN, 12 V, 2.0 A

For complete documentation, see the data sheet.

Typical applications are DC-DC converters and power management in portable and battery powered products such as cellular and cordless phones, PDAs, computers, printers, digital cameras and MP3 players. Other applications are low voltage motor controls in mass storage products such as disc drives and tape drives. In the automotive industry they can be used in air bag deployment and in the instrument cluster. The high current gain allows e2PowerEdge devices to be driven directly from PMU's control outputs, and the Linear Gain (Beta) makes them ideal components in analog amplifiers.

Features

- High Current, Low VCE(sat), ESD Robust, High Current Gain, High Cut Off Frequency, Low Profile Package, Linear Gain (Beta)

Benefits

- Improved Circuit Efficiency, Decreased Battery Charge Time, Reduce component count, High Frequency Switching, Smaller Portable Product, No distortion

Applications

- Load Switching, Battery Charging, External Pass Transistor, DC/DC Converter, Complimentary Driver, Current Extention & Low Drop Out Regulation, Cathode Florescent Lamp drive, Peripheral Driver - LEDs, Motors, Relays

Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	Polarity	Type	V _{CE(sat)} Max (V)	I _C Cont. (A)	V _{CEO} Min (V)	V _{CE0} (V)	V _{EBO} (V)	V _{BE(sat)} (V)	V _{BE0} (V)	h _{FE} Min	h _{FE} Max	f _T Min (MHz)	P _{TM} Max (W)	Package Type
NSS12201LT1G	0.1485	Pb-free Halide free non AEC-Q and PPAP	Active	NPN	Low V _{CE(sat)}	0.05	2	12	12	6	0.9	0.9	200	-	150	0.54	SOT-23-3

For more information please contact your local sales support at www.onsemi.com.

Created on: 7/24/2021