

Product Overview

NVMFS5C410NL: Single N-Channel Power MOSFET 40V, 330A, 0.82mΩ

For complete documentation, see the data sheet.

Automotive Power MOSFET in a 5x6mm flat lead package designed for compact and efficient designs and including high thermal performance. Wettable Flank Option available for Enhanced Optical Inspection. AEC-Q101 Qualified MOSFET and PPAP capable suitable for automotive applications.

Features

- Small Footprint (5x6 mm)
- Low RDS(on)
- Low QG and Capacitance
- NVMFS5C410NLWF - Wettable Flank Option
- AEC-Q101 Qualified and PPAP Capable
- RoHS Compliant

Benefits

- Compact Design
- Minimize Conduction Losses
- Minimize Driver Losses
- Enhanced Optical Inspection
- Automotive qualified

Applications

- Reverser Battery protection
- Power switches (High Side Driver, Low Side Driver, H-Bridges etc.)
- Switching power supplies

End Products

- Solenoid Driver – ABS, Fuel injection
- Motor Control – EPS, Wipers, Fans, Seats, etc.
- Load Switch – ECU, Chassis, Body

Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	Channel Polarity	Configuration	V _{DS(BR)DSS} Min (V)	V _{GS} Max (V)	V _{GS(th)} Max (V)	I _D Max (A)	P _D Max (W)	R _{DS(on)} Max @ V _{GS} = 2.5 V (mΩ)	R _{DS(on)} Max @ V _{GS} = 4.5 V (mΩ)	R _{DS(on)} Max @ V _{GS} = 10 V (mΩ)	Q _g Typ @ V _{GS} = 4.5 V (nC)	Q _g Typ @ V _{GS} = 10 V (nC)	C _{iss} Typ (pF)	Package Type
NVMFS5C410NLAFT1G		AEC Qualified PPAP Capable Pb-free Halide free	Active	N-Channel	Single	40	20	2	315	167	-	1.2	0.82	-	143	8862	SO-8FL / DFN-5
NVMFS5C410NLWFAFT1G		AEC Qualified PPAP Capable Pb-free Halide free	Active	N-Channel	Single	40	20	2	315	167	-	1.2	0.82	-	143	8862	SO-8FL / DFN-5
NVMFS5C410NLWFT3G		AEC Qualified PPAP Capable Pb-free Halide free	Active	N-Channel	Single	40	20	2	315	167	-	1.2	0.82	-	143	8862	SO-8FL / DFN-5

For more information please contact your local sales support at www.onsemi.com.

Created on: 6/4/2020