

Product Overview

NVTFS5811NL: Power MOSFET 40V, 40A, 6.7 mOhm, Single N-Channel, u8FL, Logic Level.

For complete documentation, see the data sheet.



Automotive Power MOSFET in a 3x3mm flat lead package designed for compact and efficient designs and including high thermal performance. Wettable Flank Option available for Enhanced Optical Inspection. AEC-Q101 Qualified MOSFET and PPAP capable suitable for automotive applications.

Features

- Low on resistance
- High current capability
- 100% avalanche tested

Benefits

- Minimal conduction losses
- Robust load performance
- Safeguards against voltage overstress failures

Applications

- motor driver

End Products

- Automotive motor control

Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	Channel Polarity	Configuration	$V_{DS(s)}$ Min (V)	V_{GS} Max (V)	$V_{GS(th)}$ Max (V)	I_D Max (A)	P_D Max (W)	$R_{DS(on)}$ Max @ $V_{GS} = 2.5V$ (mΩ)	$R_{DS(on)}$ Max @ $V_{GS} = 4.5V$ (mΩ)	$R_{DS(on)}$ Max @ $V_{GS} = 10V$ (mΩ)	Q_g Typ @ $V_{GS} = 4.5V$ (nC)	Q_g Typ @ $V_{GS} = 10V$ (nC)	C_{iss} Typ (pF)	Package Type
NVTFS5811NLTAG		AEC Qualified PPAP Capable Pb-free Halide free	Active	N-Channel	Single	40	20	2.2	40	21		10	6.7	17	30	1570	WDF N-8 / u8FL

For more information please contact your local sales support at www.onsemi.com.

Created on: 6/4/2020