

## Product Overview

### AMIS-49200: Fieldbus Physical Layer Medium Access Unit (MAU)

For complete documentation, see the data sheet.

AMIS-49200 and AMIS-49250 Fieldbus MAU (media access units) are transceiver chips for low speed FOUNDATION Fieldbus® and Profibus® PA devices. AMIS-49200 was designed to be a near pin-for-pin replacement of the Yokogawa  $\mu$ SAA22Q MAU. 'Near pin-for-pin' means that associated component values may change, but no board changes are required. AMIS-49250 is a small, micro-lead frame version, in a 7.0 x 7.0 mm NQFP-44 package.

### Features

- All node power can be supplied by the bus, via the AMIS-492x0
- Current consumption 500  $\mu$ A (typ)
- VCC voltage: 6.2 V to 4.75 V
- VDD voltage: 5.5 V to 2.7 V
- Compatible with IEC 1158-2 and ISA 50.02
- Shunt regulator
- Voltage reference (internal only)
- Series regulator
- Bandpass filter
- Slew rate control

For more features, see the data sheet

### Applications

- Process automation
- Pressure and temperature monitoring

### End Products

- Paper manufacturing
- Control or flow metering devices for oil refineries
- Natural gas production

### Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	Data Transmission Standard	Data Rate	Number of Drivers	Number of Receivers	V <sub>CC</sub> Min (V)	V <sub>CC</sub> Max (V)	t <sub>PLH</sub> Max ( $\mu$ s)	I <sub>O</sub> Max ( $\mu$ A)	I <sub>IH</sub> Max (mA)	Package Type
AMIS-49200-XTD	9.78	Pb-free Halide free non AEC-Q and PPAP	Active	MAU	31.25 kbps	1	1	4.75	6.2	4.7	30000	0.001	LQFP-44
AMIS-49200-XTP	9.78	Pb-free Halide free non AEC-Q and PPAP	Active	MAU	31.25 kbps	1	1	4.75	6.2	4.7	30000	0.001	LQFP-44
AMIS-49250-XTP	9.78	Pb-free Halide free non AEC-Q and PPAP	Active	MAU	31.25 kbps	1	1	4.75	6.2	4.7	30000	0.001	NQFP-44

For more information please contact your local sales support at [www.onsemi.com](http://www.onsemi.com).

Created on: 10/17/2021