

Product Overview

CAV24C32: EEPROM Serial 32-Kb I²C - Automotive Grade

For complete documentation, see the data sheet.

The CAV24C32 is a EEPROM Serial 32-Kb I²C - Automotive Grade devices, internally organized as 4096 words of 8 bits each. It features a 32-byte page write buffer and supports the Standard (100 kHz) and Fast (400 kHz) I²C protocol. External address pins make it possible to address up to eight CAV24C32 devices on the same bus.

Features

- Automotive Temperature Grade 1 (-40°C to +125°C)
- 2.5 V to 5.5 V Supply Voltage Range
- This Device is Pb-Free, Halogen Free/BFR Free, and RoHS Compliant
- Supports Standard and Fast I²C Protocol
- 32-Byte Page Write Buffer
- Hardware Write Protection for Entire Memory
- CAV Prefix for Automotive and Other Applications Requiring Site and Change Control
- Schmitt Triggers and Noise Suppression Filters on I²C Bus Inputs(SCL and SDA)
- Low Power CMOS Technology
- 1,000,000 Program/Erase Cycles

For more features, see the data sheet

Benefits

- Allows the use in safety critical application.
- Single power supply from 2.5V to 5.5V. Functional over the entire Temperature range.
- Space-Efficient Packaging

Applications

- Door module
- Seat control unit
- Immobilizer unit
- Wiper module
- Fan control unit

Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	Type	Density	Organization	Data Transmission Standard	f _{cycle} Max (kHz)	t _{ACC} Max ns	V _{CC} Min (V)	V _{CC} Max (V)	I _{standby} Max (μA)	I _{act} Max (mA)	T Min (°C)	T Max (°C)	Package Type
CAV24C32C4CTR	0.3467	AEC Qualified PPAP Capable Pb-free Halide free	Active	Serial	32 kb	4k x 8	I2C	400	900	2.5	5.5	5	2	-40	125	WLC SP-4
CAV24C32C5ATR	0.35	AEC Qualified PPAP Capable Pb-free Halide free	Active	Serial	32 kb	4k x 8	I2C	400	900	2.5	5.5	5	2	-40	125	WLC SP-5
CAV24C32C5CTR		AEC Qualified PPAP Capable Pb-free Halide free	Active	Serial	32 kb	4k x 8	I2C	400	900	2.5	5.5	5	2	-40	125	WLC SP-5
CAV24C32WE-GT3	0.2861	AEC Qualified PPAP Capable Pb-free Halide free	Active	Serial	32 kb	4k x 8	I2C	400	900	2.5	5.5	5	2	-40	125	SOIC-8
CAV24C32YE-GT3	0.3011	AEC Qualified PPAP Capable Pb-free Halide free	Active	Serial	32 kb	4k x 8	I2C	400	900	2.5	5.5	5	2	-40	125	TSS OP-8

For more information please contact your local sales support at www.onsemi.com.

Created on: 3/29/2020