

## Product Overview

### NCP13992: Current Mode Resonant Controller with Integrated High Voltage Drivers, High Performance

For complete documentation, see the data sheet.

The NCP13992 is a high performance current mode controller for half bridge resonant converters. This controller implements 600 V gate drivers, simplifying layout and reducing external component count. The built-in Brown-Out input function eases implementation of the controller in all applications. In applications where a PFC front stage is needed, the NCP13992 features a dedicated output to drive the PFC controller. This feature together with dedicated quiet skip mode technique further improves light load efficiency of the whole application. The NCP13992 provides a suite of protection features allowing safe operation in any application. This includes: overload protection, over-current protection to prevent hard switching cycles, brown-out detection, open optocoupler detection, automatic dead-time adjust, overvoltage (OVP) and overtemperature (OTP) protections.

#### Features

- Quiet Skip Mode technique
- Current Mode Control Scheme
- Automatic Dead-time with Maximum Dead-time Clamp

#### Applications

- Half Bridge Resonant Converter
- Offline Power Supply

#### Benefits

- Improves Light Load Efficiency avoiding transformer acoustic noise
- Built-in safety protection, improved transient response
- Improved efficiency

#### End Products

- Notebook Adapters
- LCD, LED and OLED TV
- High Power AC/DC Adapter
- Industrial and Medical Power Supply
- Computing Power Supply

### Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	Topology	Control Mode	f <sub>sw</sub> Typ (kHz)	Stand-by Mode	UVLO (V)	Short Circuit Protection	Latch	Soft Start	V <sub>CC</sub> Max (V)	Drive Cap. (mA)	Package Type
NCP13992AADR2G	0.7333	Pb-free Halide free	Active	Half-Bridge	Current Mode	Up to 750 kHz	Yes	8.9	Yes	Yes	Yes	20	500 / 1000	SOIC-16 NB
NCP13992ABDR2G	0.7333	Pb-free Halide free	Active	Half-Bridge	Current Mode	Up to 750 kHz	Yes	8.9	Yes	No	Yes	20	500 / 1000	SOIC-16 NB
NCP13992ACDR2G	0.7333	Pb-free Halide free	Active	Half-Bridge	Current Mode	Up to 750 kHz	Yes	8.9	Yes	Yes	Yes	20	500 / 1000	SOIC-16 NB
NCP13992AEDR2G	0.7333	Pb-free Halide free	Active											SOIC-16 NB
NCP13992AFDR2G	0.7333	Pb-free Halide free	Active											SOIC-16 NB
NCP13992AGDR2G	0.7333	Pb-free Halide free	Active											SOIC-16 NB
NCP13992AHDR2G	0.7333	Pb-free Halide free	Active											SOIC-16 NB

For more information please contact your local sales support at [www.onsemi.com](http://www.onsemi.com).

Created on: 7/15/2020