

## Product Overview

### NCS20071: Operational Amplifier, Wide supply range, 3Mhz CMOS Op-Amp

For complete documentation, see the data sheet.

The NCS20071/2/4 series operational amplifiers provide rail-to-rail output operation, 3 MHz bandwidth, and are available in single, dual, and quad configurations. Rail-to-rail operation enables the user to make optimal use of the entire supply voltage range while taking advantage of 3 MHz bandwidth. The NCS2007x can operate on supply voltages as low as 2.7 V over the temperature range of -40°C to 125°C. At a 2.7 V supply, the high bandwidth provides a slew rate of 2.8 V/μs while only consuming 405 μA of quiescent current per channel. The wide supply range allows the NCS2007x to run on supply voltages as high as 36 V, making it ideal for a broad range of applications. Since this is a CMOS device, high input impedance and low bias currents make it ideal for interfacing to a wide variety of signal sensors. The NCx2007x devices are available in a variety of compact packages. Automotive qualified options are available under the NCV prefix.

Product Family:

&nbsp;  
NCS20071  
NCS20072  
NCS20074

Channel  
1  
2  
4

Packages  
SOT553, SOT23-5  
SOIC-8, Micro-8, TSSOP-8  
TSSOP-14, SOIC-14

### Features

- Wide Supply Range: 2.7 V to 36 V
- Wide Bandwidth: 3 MHz typical at  $V_s = 2.7$  V
- Low Supply Current: 405 μA per channel at  $V_S = 2.7$  V
- High Slew Rate: 2.8 V/μs typical at  $V_S = 2.7$  V
- Low Input Bias Current: 5 pA typical
- Rail-To-Rail Output
- Wide Temperature Range: -40°C to 125°C
- NCV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q100 Qualified and PPAP Capable

### Applications

- Current Sensing
- Signal Conditioning
- Automotive
- Lighting

### Benefits

- Wide supply range suitable for a variety of applications
- Compatible with high speed signals up to 3 MHz
- Low current consumption
- High large signal bandwidth
- High input impedance
- Wide output range
- Functional over wide temperature range
- Meets automotive standards

### End Products

- Notebook Computers
- Portable Instruments
- Power Supplies

## Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	Rail to Rail	Channels	V <sub>S</sub> Min (V)	V <sub>S</sub> Max (V)	I <sub>q</sub> Typ (mA)	V <sub>OS</sub> Max (mV)	GBW Typ (MHz)	SR Typ (V/μs)	I <sub>O</sub> Typ (mA)	ΔV <sub>OS</sub> /ΔT (μV/°C)	e <sub>N</sub> (nV/√Hz)	I <sub>bias</sub> Typ (pA)	CMRR Typ (dB)	Architecture	Temperature Range (°C)	Package Type
NCS20071SN2T1G	0.204	Pb-free Halide free	Active	Output	1	2.7	36	0.48 0.43	3.5	3	2.4	50	2	30	5	135	CMOS	-40 to 125	TSOP-5
NCS20071XV53T2G	0.204	Pb-free Halide free	Active	Output	1	2.7	36	0.43	3.5	3	2.4	50	2	30	5	135	CMOS	-40 to 125	SOT-553
NCV20071SN2T1G	0.2133	AEC Qualified PPAP Capable Pb-free Halide free	Active	Output	1	2.7	36	0.41	4	3	2.4	50	2	30	5	145	CMOS	-40 to 125	TSOP-5
NCV20071XV53T2G	0.2133	AEC Qualified PPAP Capable Pb-free Halide free	Active	Output	1	2.7	36	0.43	3.5	3	2.4	50	2	30	5	135	CMOS	-40 to 125	SOT-553

For more information please contact your local sales support at [www.onsemi.com](http://www.onsemi.com).

Created on: 8/4/2020