

## Product Overview

### NCN5130: Full Featured KNX Transceiver for Twisted Pair Networks

For complete documentation, see the data sheet.



NCN5130 is a receiver-transmitter IC suitable for use in KNX twisted pair networks (KNX TP1-256). NCN5130 embeds both PHY and MAC layers and handles the transmission and reception of data on the bus. It generates from the unregulated bus voltage stabilized voltages for its own power needs as well as to power external devices. NCN5130 assures safe coupling to and decoupling from the bus. Various monitors (bus voltage, current, temperature...) are made available through an analog pin.

#### Features

- KNX certified TP transceiver with embedded PHY and MAC layers (TP1-256) . 9600 Bauds communication speed.
- Two high efficient DC-DC converters + one linear regulator :- DC-DC1 : fixed 3.3 V- DC-DC2 : adjustable between 1.2 and 21 V- 20V linear regulator
- Bus Current Consumption up to 40 mA
- Supervision of temperature, KNX bus voltage and current
- Control and monitoring of power regulators
- Buffering of sent data frames (extended frames supported)
- Selectable UART/SPI interface and baud rate to host controller.
- Comprehensive clocking system - Operates with industry standard low cost 16 MHz quartz - Can generate 8/16 MHz clock for the external MCU
- Extended ambient temperature range -40 C to +105 C

#### Applications

- Home Automation
- Smart Building

#### Benefits

- NCN5130 can be used in any TP1-256 application
- Most KNX applications can directly be supplied from the NCN5130 removing the need for external costly power supply. Best in Class overall system efficiency.
- Enables variety of high end/ power demanding KNX applications.

#### End Products

- Smart lighting & switches
- Ventilation and air conditioning
- Thermostats
- Alarms and smoke detectors
- Shutters and blinds

#### Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	Data Transmission Standard	Data Rate	Number of Drivers	Number of Receivers	V <sub>CC</sub> Min (V)	V <sub>CC</sub> Max (V)	t <sub>PLH</sub> Max (µs)	I <sub>O</sub> Max (µA)	I <sub>IH</sub> Max (mA)	Package Type
NCN5130MNTWG		AEC Qualified Pb-free Halide free non AEC-Q and PPAP	Active	KNX	9600 baud	1	1	3.13	3.47				QFN-40

For more information please contact your local sales support at [www.onsemi.com](http://www.onsemi.com).

Created on: 5/8/2021