

## Product Overview

### NCP1522B: Buck Converter, DC-DC, 3 MHz, 600 mA

For complete documentation, see the data sheet.

The NCP1522B step-down DC-DC converter is a monolithic integrated circuit optimized for portable applications powered from one cell Li-Ion or three cell Alkaline/NiCd/NiMH batteries. The part, available in adjustable output voltage versions ranging from 0.9 V to 3.3 V, is able to deliver up to 600 mA. It uses synchronous rectification to increase efficiency and reduce external part count. The device also has a built-in 3 MHz (nominal) oscillator which reduces component size by allowing smaller inductors and capacitors. Automatic switching PWM/PFM mode offers improved system efficiency. Additional features include integrated soft-start, cycle-by-cycle current limiting and thermal shutdown protection. The NCP1522B is available in a space saving, low profile TSOP5 and UDFN6 packages.

#### Features

- 94% efficiency, 50 uA quiescent current, 0.3 uA shutdown current
- 3.0 MHz switching frequency
- Auto-switching between PWM and PFM mode at light load conditions
- Adjustable output voltage from 0.9V to 3.3V

#### Applications

- Power supply for application processor
- Power supply for processor with low core voltage

#### Benefits

- Extends battery life and 'play-time'
- Allows use of smaller inductor (down to 1uH) and capacitor
- Low power consumption at light loading

#### End Products

- Cellular phones, smart phones, and PDAs
- MP3 players and portable audio systems
- Digital still cameras and video cameras

### Part Electrical Specifications

Product	Compliance	Status	Topology	Control Mode	V <sub>CC</sub> Min (V)	V <sub>CC</sub> Max (V)	V <sub>o</sub> Typ (V)	I <sub>o</sub> Typ (A)	Efficiency (%)	f <sub>sw</sub> Typ (kHz)	Package Type
NCP1522BMUTBG	Pb-free Halide free	Active	Step-Down	Voltage Mode	2.7	5.5	0.9 to 3.3	0.6	95	3000	UDFN-6
NCP1522BSNT1G	Pb-free Halide free	Active	Step-Down	Voltage Mode	2.7	5.5	0.9 to 3.3	0.6	95	3000	TSOP-5 / SOT-23-5

For more information please contact your local sales support at [www.onsemi.com](http://www.onsemi.com).

Created on: 9/19/2019