

Product Overview

NCP1547: 1.5 A, 340 kHz, Low Voltage Buck Regulator with Synchronization Capability

For complete documentation, see the data sheet.

The NCP1547 is a 1.5 A buck regulator IC operating at a fixed frequency of 340 kHz. The device employs the V2™ control architecture to provide unmatched transient response, the best overall regulation and the simplest loop compensation. The NCV8842 accommodates input voltages from 4.0 V to 40 V and contains synchronization circuitry. The on-chip NPN transistor is capable of providing a minimum of 1.5 A of output current and is biased by an external boost capacitor to ensure saturation, thus minimizing on-chip power dissipation. Protection circuitry includes thermal shutdown, cycle-by-cycle current limiting and frequency foldback short-circuit protection.

Features

- V2™ Control Architecture
 - 2.0% Error Amp Reference Voltage Tolerance
 - Cycle-by-Cycle Current Limiting
 - Switch Frequency Decrease of 4:1 in Short Circuit
 - Bootstrapped Operation (BOOST)
 - Synchronization to External Clock (SYNC)
 - 1.0 A Shutdown Quiescent Current
 - Thermal Shutdown
 - Soft-Start
 - Pb-Free Packages are Available
- For more features, see the data sheet

Applications

- Industrial Control
- Point-of-Load Voltage Regulation
- Consumer Audio and video
- Computer and Computer Peripheral
- Automotive Version Available As NCV8843

Benefits

- Ultra-fast Transient Response, Improved Regulation and Simplified Design
- Tight Output Regulation
- Limits Switch and Inductor Current
- Reduces Short Circuit Power Dissipation
- Increased Efficiency and Minimized On-Chip Power Dissipation
- Synchronization to External Clock (SYNC)
- Minimize Current Consumption when SHDNB is Asserted
- Protect IC from Over-Temperature
- Decrease Inrush Current and Minimize Output Over-shoot During Start-Up

End Products

- Dc-dc power supplies

For more information please contact your local sales support at www.onsemi.com.

Created on: 8/13/2020