

## Product Overview

### 1N5404: Standard Recovery Rectifier, 400 V, 3.0 A

For complete documentation, see the data sheet.

The Standard Recovery Rectifier is designed for use in power supplies and other applications.

### Features

- High Current to Small Size
- High Surge Current Capability
- Low Forward Voltage Drop
- Void-Free Economical Plastic Package
- Available in Volume Quantities
- Plastic Meets UL 94V-0 for Flammability
- Mechanical Characteristics:
- Case: Epoxy, Molded
- Weight: 1.1 gram (approximately)
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable
- Lead and Mounting Surface Temperature for Soldering Purposes: 220°C Max. for 10 Seconds, 1/16" from case

For more features, see the data sheet

Part Electrical Specifications											
Product	Pricing (\$/Unit)	Compliance	Status	Type	$I_{O(rec)}$ Max (A)	$t_{rr}$ Max (ns)	$V_{RRM}$ Max (V)	$V_{FM}$ Max (V)	$I_{FSM}$ Max (A)	$I_R$ Max (mA)	Package Type
1N5404G	0.0693	Pb-free Halide free non AEC-Q and PPAP	Active	Standard Recovery	3		400	1	200	0.01	Axial Lead-2
1N5404RLG	0.0616	Pb-free Halide free non AEC-Q and PPAP	Active	Standard Recovery	3		400	1	200	0.01	Axial Lead-2

For more information please contact your local sales support at [www.onsemi.com](http://www.onsemi.com).

Created on: 1/21/2021