

Product Overview

MBR1045: Schottky Barrier Rectifier, 10 A, 45 V

For complete documentation, see the data sheet.

This Schottky Rectifier uses the Schottky Barrier principle with a platinum barrier metal.

Features

- Guardring for Stress Protection
- Low Forward Voltage
- 150 C Operating Junction Temperature
- Epoxy Meets UL94, VO at 1/8" Mechanical Characteristics:
- Case: Epoxy, Molded
- Weight: 1.9 grams (approximately)
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable
- Lead Temperature for Soldering Purposes: 260 °C Max. for 10 Seconds
- Marking: B1035, B1045
- Pb-Free Packages are Available

For more features, see the data sheet

Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	Configuration	V_{RRM} Min (V)	V_F Max (V)	I_{RM} Max (μ A)	$I_{O(max)}$ Max (A)	I_{FSM} Max (A)	t_r Max (ns)	C_j Max (pF)	Package Type
MBR1045G	0.2791	Pb-free	Active	Single	45	0.84	100	10	150	-	-	TO-220-2

For more information please contact your local sales support at www.onsemi.com.

Created on: 3/30/2020