

Product Overview

MBR20L45: Schottky Barrier Rectifier, Dual, L-Series, 20 A, 90 V

For complete documentation, see the data sheet.

Enhanced Schottky rectifiers with lower VF, higher surge, and lower IR parameters

Features

- Low Forward Voltage
 - Low Power Loss/High Efficiency
 - High Surge Capacity
 - 150C Operating Junction Temperature
 - 20A Total (10A Per Diode Leg)
 - Guard-Ring for Stress Protection Mechanical Characteristics:
 - Case: Epoxy, Molded
 - Epoxy Meets UL 94 V-0 @ 0.125 in
 - Weight (Approximately): 1.9 Grams
 - Finish: All External Surfaces Corrosion Resistant and TerminalLeads are Readily Solderable
- For more features, see the data sheet

Benefits

- Lower forward power loss

Applications

- Power Supply - Output Rectification
- Power Management
- Instrumentation

End Products

- Power Supply

Part Electrical Specifications

Product	Compliance	Status	Configurati on	V_{RRM} Min (V)	V_F Max (V)	I_{RM} Max (μ A)	$I_{O(rec)}$ Max (A)	I_{FSM} Max (A)	t_r Max (ns)	C Max (pF)	Package Type
MBR20L45CTG	Pb-free	Active	Common Cathode	45	0.63	500	20	180	-	-	TO-220-3
MBRF20L45CTG	Pb-free	Active	Common Cathode	45	0.63	500	20	180	-	-	TO-220-3 FullPak

For more information please contact your local sales support at www.onsemi.com.

Created on: 10/18/2019