

## Product Overview

### MBRS120: Schottky Power Rectifier, Surface Mount, 1.0 A, 20 V

For complete documentation, see the data sheet.

The Schottky Rectifier employs the Schottky Barrier principle in a large area metal-to-silicon power diode. The Schottky Rectifier's state-of-the-art geometry features epitaxial construction with oxide passivation and metal overlay contact. It is ideally suited for low voltage, high frequency rectification, or as free wheeling and polarity protection diodes in surface mount applications where compact size and weight are critical to the system.

### Features

- Small Compact Surface Mountable Package with J-Bend Leads
- Rectangular Package for Automated Handling
- Highly Stable Oxide Passivated Junction
- Very Low Forward Voltage Drop(0.55 Volts Max @ 1.0 A, T<sub>J</sub> = 25°C)
- Excellent Ability to Withstand Reverse Avalanche Energy Transients
- Guardring for Stress ProtectionMechanical Characteristics:
- Case: Epoxy, Molded
- Weight: 95 mg (approximately)
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable
- Lead and Mounting Surface Temperature for Soldering Purposes: 260°C Max. for 10 Seconds

For more features, see the data sheet

### Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	Configuration	V <sub>RRM</sub> Min (V)	V <sub>F</sub> Max (V)	I <sub>RM</sub> Max (μA)	I <sub>O(rec)Max</sub> (A)	I <sub>FSM</sub> Max (A)	t <sub>rr</sub> Max (ns)	C <sub>j</sub> Max (pF)	Package Type
MBRS120T3G	0.0725	Pb-free	Active	Single	20	0.6	1000	1	40	-	-	SMB-2
		Halide free										
SBR8120NT3G	0.0356	AEC Qualified PPAP Capable Pb-free Halide free	NEW	Single	20	0.6	1000	1	40	-	-	SMB-2

For more information please contact your local sales support at [www.onsemi.com](http://www.onsemi.com).

Created on: 7/7/2020