

Product Overview

NCP5662: LDO Regulator, 2 A, Low Noise, with Enable

For complete documentation, see the data sheet.

The NCP5662 is a high performance, low dropout (LDO) linear voltage regulator designed for high power applications that require up to 2.0 A current. It is offered in both fixed and adjustable output versions. With output voltages as low as 0.9 V and ultra-fast response times for load transients, the NCP5662 also provides additional features such as Enable and Error Flag (for the fixed output version), increasing the utility of this device. A thermally robust, 5 pin D2Pak, combined with an architecture that offers low ground current (independent of load), provides for a superior high-current LDO solution.

Features

- UltraFast Transient Response (Settling Time: 1 - 3 us)
- Low Noise Without Bypass Capacitor (26 uVrms)
- Low Ground Current Independent of Load (3.0 mA Maximum)
- Fixed/Adjustable Output Voltage Versions
- Enable Function
- Error Flag (Fixed Output Version)
- Current Limit Protection
- Thermal Shutdown Protection (160C)
- 0.9 V Reference Voltage for Ultra-Low Output Operation
- Power Supply Rejection Ratio > 65 dB

For more features, see the data sheet

Applications

- Servers and Networking Systems
- Gaming and STB Modules
- Automotive

Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	Output	Polarity	V _O (V)	I _O Typ (A)	V _I Min (V)	V _I Max (V)	V _{DO} Typ (V)	I _Q Typ (mA)	PSRR (dB)	Noise (μV _{rms})	Enable	PowerGood	Application	Package Type
NCP5662DS28R4G	0.9652	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	2.8	2	2	9	1	1.3	65	26	Yes	Yes		D ² PAK-5
NCP5662DS30R4G	0.9652	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	3	2	2	9	1	1.3	65	26	Yes	Yes		D ² PAK-5
NCP5662MN15R2G	0.9277	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	1.5	2	2	9	1	1.3	65	26	Yes	Yes		DFN-8
NCV5662DSADJR4G	0.9246	AEC Qualified PPAP Capable Pb-free Halide free	Active	Single	Positive	Adj	2	2	9	1	1.3	65	26	Yes	No	Automotive	D ² PAK-5

For more information please contact your local sales support at www.onsemi.com.

Created on: 8/3/2021