

NCP334

Controlled Load Switch, Ultra Small, 2.0 A, with Auto-Discharge Path

Product Overview

For complete documentation, see the data sheet.

The NCP334 and NCP335 are very low Ron MOSFETs controlled by an external logic pin, allowing optimization of battery life, and portable device autonomy. Indeed, thanks to a current consumption optimization with PMOS structure, leakage currents are eliminated by isolating connected IC on the battery when not used. Output discharge path is available in NCP335 version.

Features

- 1.2 V - 5.5 V operating range
- 42 mΩ RDS(ON) at 4.2 V
- DC current up to 2 A
- Output Auto-discharge (NCP335)

Applications

- Load Management

End Products

- Smart Phones
- Tablets

Application Diagram

