

Product Overview

NCP803: Voltage Supervisor, 3-Pin, Microprocessor, Very Low Supply Current, Reset Monitor

For complete documentation, see the data sheet.

The MAX803/NCP803 is a cost-effective system supervisor circuit designed to monitor VCC in digital systems and provide a reset signal to the host processor when necessary. No external components are required. The reset output is driven active within 10 μ sec of VCC falling through the reset voltage threshold. Reset is maintained active for a timeout period which is trimmed by factor after VCC rises above the reset threshold. The MAX803/NCP803 has an open drain active-low RESET(bar) output. The output of the MAX803/NCP803 is guaranteed valid down to VCC = 1.0 V and is available in a SOT-23 and SC-70 package. The MAX803/NCP803 is optimized to reject fast transient glitches on the VCC line. Low supply current of 0.5 μ A (VCC = 3.3 V) make this device suitable for battery powered applications.

Features

- Precision VCC Monitor for 1.5 V, 1.8V, 2.5 V, 3.0 V, 3.3 V and 5.0 V supplies
- Precision Monitoring Voltages from 1.2 V to 4.9 V Available in 100 mV Steps
- Four Guaranteed Minimum RESET Output Duration(1ms, 20ms, 100ms and 140ms)
- RESET Output Guaranteed to VCC = 1.0 V
- Low 0.5 μ A Supply Current
- VCC Transient Immunity
- Small SOT-23 and SC-70 Package
- No External Components
- Wide Operating Temperature: -40°C to 105°C

Applications

- Computers
- Embedded Systems
- Battery Powered Equipment
- Critical A Power Supply Monitoring

Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	Voltages Monitored	V _{OC} Max (V)	V _(TO) Typ (V)	I _O Typ (µA)	Reset Active State	Reset Timer	Manual Reset	Watchdog Timer	Package Type
NCP803SN120T1G	0.236	Pb-free	Active	1	5.5	1.2	0.5	Low	Yes	No	No	SOT-23-3
		Halide free non AEC-Q and PPAP										
NCP803SN160T1G	0.1707	Pb-free	Active	1	5.5	1.6	0.5	Low	Yes	No	No	SOT-23-3
		Halide free non AEC-Q and PPAP										
NCP803SN232T1G	0.1711	Pb-free	Active	1	5.5	2.32	0.5	Low	Yes	No	No	SOT-23-3
		Halide free non AEC-Q and PPAP										
NCP803SN263T1G	0.2095	Pb-free	Active	1	5.5	2.63	0.5	Low	Yes	No	No	SOT-23-3
		Halide free non AEC-Q and PPAP										
NCP803SN293D1T1G	0.1589	Pb-free	Active	1	5.5	2.93	0.5	Low	Yes	No	No	SOT-23-3
		Halide free non AEC-Q and PPAP										
NCP803SN293D2T1G		Pb-free	Active	1	5.5	2.93	0.5	Low	Yes	No	No	SOT-23-3
		Halide free non AEC-Q and PPAP										
NCP803SN293D3T1G	0.1589	Pb-free	Active	1	5.5	2.93	0.5	Low	Yes	No	No	SOT-23-3
		Halide free non AEC-Q and PPAP										
NCP803SN293T1G	0.1707	Pb-free	Active	1	5.5	2.93	0.5	Low	Yes	No	No	SOT-23-3
		Halide free non AEC-Q and PPAP										
NCP803SN293T3G		Pb-free	Active	1	5.5	2.93	0.5	Low	Yes	No	No	SOT-23-3
		Halide free non AEC-Q and PPAP										
NCP803SN308T1G	0.2095	Pb-free	Active	1	5.5	3.08	0.5	Low	Yes	No	No	SOT-23-3
		Halide free non AEC-Q and PPAP										
NCP803SN400T1G		Pb-free	Active	1	5.5	4	0.5	Low	Yes	No	No	SOT-23-3
		Halide free non AEC-Q and PPAP										
NCP803SN438T1G	0.1735	Pb-free	Active	1	5.5	4.38	0.5	Low	Yes	No	No	SOT-23-3
		Halide free non AEC-Q and PPAP										
NCP803SN463D1T1G	0.236	Pb-free	Active	1	5.5	4.63	0.5	Low	Yes	No	No	SOT-23-3
		Halide free non AEC-Q and PPAP										
NCP803SN463T1G	0.1675	Pb-free	Active	1	5.5	4.63	0.5	Low	Yes	No	No	SOT-23-3
		Halide free non AEC-Q and PPAP										

For more information please contact your local sales support at www.onsemi.com.

Created on: 1/21/2021