

Product Overview

XGS 16000: CMOS Image Sensor, 16 MP, Global Shutter

For complete documentation, see the data sheet.

Advance Information

The XGS 16000 is a 16.0 Mp (4000 x 4000) CMOS image sensor in 1.1 inch optical format, supporting up to 65 frame per second readout at full resolution.

The device provides high resolution, global shutter imaging with high readout speed for industrial imaging customers. A compact package design and low power footprint make the device compatible with a 29 x 29 mm² camera footprint. Three speed grades are available to match device output to key computer interfaces and application requirements.

The XGS 16000 shares a common design and footprint with other members of the XGS family, allowing one camera design to support multiple resolutions to simplify and speed time to market for new camera designs.

The XGS 16000 is available in a 163-pin iLGA package in both monochrome and Bayer color configurations.

Features

- Advanced 3.2 μm global shutter pixel
- Energy efficient design
- Available speed grades
- Compact package
- 1:1 (square) aspect ratio

Applications

- Image capture

Benefits

- High resolution with high image quality and uniformity
- Reduced power and thermal footprints
- Match to key computer interface and application requirements
- Compatible with 29 x 29 mm² camera design
- Maximize image capture within lens optical circle

End Products

- Industrial cameras and systems
- Inspection system (food, bottles, recycling labels, etc.)
- Security cameras and systems
- Machine Vision camera

Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	Type	Megapixels	Frame Rate (fps)	Optical Format	Shutter Type	Pixel Size (μm)	Output Interface	Color	Package Type
NOIX1SE016KB-LTI-E		Pb-free Halide free non AEC-Q and PPAP	Active	CMOS	16	65	1.1 inch	Global Shutter	3.2 x 3.2	HiSPi™	Bayer Color	ILGA163 21.5x19.5, 1P
NOIX1SN016KB-LTI-E		Pb-free Halide free non AEC-Q and PPAP	Active	CMOS	16	65	1.1 inch	Global Shutter	3.2 x 3.2	HiSPi™	Mono	ILGA163 21.5x19.5, 1P

For more information please contact your local sales support at www.onsemi.com.

Created on: 10/29/2020