


ARX3A0

CMOS Image Sensor, Ultra-Low-Power, 560 x 560, 360 fps



Product Overview

For complete documentation, see the data sheet.

The ARX3A0 is a breakthrough CMOS imaging sensor. Designed to be ultra-miniature (1/10th inch optical format) and ultra-low-power, the ARX3A0 brings new options to IoT device, drones and robotics. The product has an innovative super low power mode which draws less than 3.2 mW while active, and can detect motion or changes in lighting conditions and wake the rest of the system up. With its high frame rate of 360 frames per second (fps), the ARX3A0 can behave like a global shutter sensor in many circumstances, while still having all the benefits of power, size and performance of a 2.2 μm rolling shutter pixel.

Evaluation Tools

An evaluation kit and our industry-leading DevWare evaluation software are available by contacting your local ON Semiconductor sales representative.

Features

- Ultra Small 1/10.3" optical format
- Ultra Low Power Operation
- High Frame rate (360 fps)
- On-board frame buffer
- Smart wake
- MIPI interface
- Mono and RGB

Applications

- Small, low power image sensing cameras









Benefits

- Can easily fit into almost any device looking for a camera
- Perfect for battery-powered cameras
- Can make a rolling shutter sensor work like a global shutter sensor
- Allows users to read off frames at standard (30 frames per second) frame rates while still operating at 360 frames per second
- Allows end product to put entire systems to sleep except the sensor. The sensor will monitor for motion and wake the entire system.
- Compatible with the new leading interface for IoT
- have both mono and RGB version

End Products

- IoT Devices
- Robotics
- Drones
- Barcode Scanners
- Battery Powered Cameras

Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	Type	Megapixels	Frame Rate (fps)	Optical Format	Shutter Type	Pixel Size (µm)	Output Interface	Color	Package Type
ARX3A0CSSC28 SMD20		 	Active	CMOS		360	1/10 inch	Electronic Rolling	2.2 x 2.2	MIPI	RGB	
ARX3A0CSSC28 SMKA0-CR-E		 	Active	CMOS		360	1/10 inch	Electronic Rolling	2.2 x 2.2	MIPI	RGB	ODCSP-35
ARX3A0CSSM0 0SMD20		 	Active	CMOS		360	1/10 inch	Electronic Rolling	2.2 x 2.2	MIPI	Mono	
ARX3A0CSSM0 0SMKA0-CR-E		 	Active	CMOS		360	1/10 inch	Electronic Rolling	2.2 x 2.2	MIPI	Mono	ODCSP-35