

Product Overview

MC74ACT163: Synchronous Presettable Binary Counter

For complete documentation, see the data sheet.

The MC74AC161/74ACT161 and MC74AC163/74ACT163 are high-speed synchronous modulo-16 binary counters. They are synchronously presettable for application in programmable dividers and have two types of Count Enable inputs plus a Terminal Count output for versatility in forming synchronous multistage counters. The MC74AC161/74ACT161 has an asynchronous Master Reset input that overrides all other inputs and forces the outputs LOW. The MC74AC163/74ACT163 has a Synchronous Reset input that overrides counting and parallel loading and allows the outputs to be simultaneously reset on the rising edge of the clock.

Features

- Synchronous Counting and Loading
- High-Speed Synchronous Expansion
- Typical Count Rate of 125 MHz
- Outputs Source/Sink 24 mA
- ACT161 and ACT163 Have TTL Compatible Inputs
- These devices are available in Pb-free package(s). Specifications herein apply to both standard and Pb-free devices. Please see our website at www.onsemi.com for specific Pb-free orderable part numbers, or contact your local ON Semiconductor sales office or representative.

Part Electrical Specifications

Product	Compliance	Status	Type	V _{CC} Min (V)	V _{CC} Max (V)	t _{pd} Max (ns)	P _D Max (W)	I _O Max (mA)	Package Type
MC74ACT163DG	Pb-free	Active	Counter	4.5	5.5	11	0.35	24	SOIC-16
	Halide free								
MC74ACT163DR2G	Pb-free	Active	Counter	4.5	5.5	11	0.35	24	SOIC-16
	Halide free								

For more information please contact your local sales support at www.onsemi.com.

Created on: 9/18/2019