

Product Overview

MC74ACT125: Quad Buffer with 3-State Outputs

For complete documentation, see the data sheet.

Outputs Source/Sink

Features

- ACT125 Has TTL Compatible Inputs
- Pb-Free Packages are Available

Part Electrical Specifications

Product	Compliance	Status	Channels	Output	V _{CC} Min (V)	V _{CC} Max (V)	t _{pd} Max (ns)	I _O Max (mA)	Package Type
MC74ACT125DG	Pb-free	Active	4	3-State	4.5	5.5	9	24	SOIC-14
	Halide free								
MC74ACT125DR2G	Pb-free	Active	4	3-State	4.5	5.5	9	24	SOIC-14
	Halide free								
MC74ACT125DTR2G	Pb-free	Active	4	3-State	4.5	5.5	9	24	TSSOP-14
	Halide free								
NLV74ACT125DR2G	AEC Qualified	Active	4	3-State	4.5	5.5	9	24	SOIC-14
	PPAP Capable								
	Pb-free								
	Halide free								

For more information please contact your local sales support at www.onsemi.com.

Created on: 9/21/2019