

Product Overview

MC74ACT125: Quad Buffer with 3-State Outputs

For complete documentation, see the data sheet.

Outputs Source/Sink

Features

- ACT125 Has TTL Compatible Inputs
- Pb-Free Packages are Available

Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	Channels	Output	V _{CC} Min (V)	V _{CC} Max (V)	t _{pd} Max (ns)	I _O Max (mA)	Package Type
MC74ACT125DG	0.2267	Pb-free Halide free	Active	4	3-State	4.5	5.5	9	24	SOIC-14
MC74ACT125DR2G	0.1333	Pb-free Halide free	Active	4	3-State	4.5	5.5	9	24	SOIC-14
MC74ACT125DTR2G	0.16	Pb-free Halide free	Active	4	3-State	4.5	5.5	9	24	TSSOP-14
NLV74ACT125DR2G	0.2493	AEC Qualified PPAP Capable Pb-free Halide free	Active	4	3-State	4.5	5.5	9	24	SOIC-14

For more information please contact your local sales support at www.onsemi.com.

Created on: 4/6/2020