

Product Overview

NCP59800: LDO Regulator, 1 A, Low Dropout, Low Iq, Low Noise, with Enable

For complete documentation, see the data sheet.

The NCP59800 is a family of 1 A low-dropout linear regulators (LDOs) offering high power-supply ripple rejection (PSRR) and ultra-low output noise. This series of LDOs uses an advanced BiCMOS process to achieve very good electrical performance. It is an ideal choice for noise sensitive Analog RF Front-Ends used in Telecom Equipment. The NCP59800 is available in the 3 mm x 3 mm DFN8 package.

Features

- 2.2 V to 6.0 V Operating Input Voltage Range
- Low Quiescent Current of Typ. 60 μ A
- Very Low Dropout: 200 mV Typ. at Iout = 1 A (Vout = 2.5 V)
- Very Low Noise, 15 μ Vrms/V typically
- Adjustable Soft-Start
- \pm 2.5% Accuracy over the Line. Load and temperature range
- Thermal Shutdown and Current Limit Protections
- Stable with 4.7 μ F Ceramic Output Capacitor

Applications

- Telecom Infrastructure
- Audio
- High-Speed I/F (PLL/VCO)

Benefits

- Suitable for Li-ion battery or post regulation application
- Extended Battery Life
- Extended Battery Range
- Good for noise sensitive applications
- Limits the In-Rush Current
- High output voltage precision
- Protects product and system from damage
- Saves PCB space and system cost

End Products

- Telecom equipment
- Industrial Control
- Networking equipment

Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	Output	Polarity	V _O (V)	I _O Typ (A)	V _{Min} (V)	V _{Max} (V)	V _{DO} Typ (V)	I _q Typ (mA)	PSRR (dB)	Noise (μ V _{rms})	Enable	Power Good	Package Type
NCP59800BMNADJTAG		Pb-free Halide free	Active	Single	Positive	Adj	1	2.2	6	0.2	0.06	63	15	Yes	No	DFN-8
NCP59800BMNADJTBG	0.1933	Pb-free Halide free	Active	Single	Positive	Adj	1	2.2	6	0.2	0.06	63	15	Yes	No	DFN-8

For more information please contact your local sales support at www.onsemi.com.

Created on: 12/14/2019