



DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	2.90	3.10	0.114	0.122
B	2.90	3.10	0.114	0.122
C	0.80	1.10	0.031	0.043
D	0.05	0.15	0.002	0.006
F	0.40	0.70	0.016	0.028
G	0.65 BSC		0.026 BSC	
L	4.90 BSC		0.193 BSC	
M	0°	6°	0°	6°

NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: MM
3. DIMENSION "A" DOES NOT INCLUDE MOLD FLASH, PROTRUSIONS OR GATE BURRS. MOLD FLASH OR GATE BURRS SHALL NOT EXCEED 0.15(.006) PER SIDE.
4. DIMENSION "B" DOES NOT INCLUDE INTERLEAD FLASH OR PROTRUSION. INTERLEAD FLASH OR PROTRUSION SHALL NOT EXCEED 0.25(.010) PER SIDE.
5. TERMINAL NUMBERS ARE SHOWN FOR REFERENCE ONLY.
6. DIMENSION "A" AND "B" ARE TO BE DETERMINED AT DATUM PLANE $-W-$
7. 948R-01 OBSOLETE. NEW STANDARD IS 948R-02.

CASE NO.	948R-02
STATUS	
NEW STD	
USED ON	



ISSUE	REVISION	COORD/ DATE
0	RELEASED FOR PRODUCTION. REQ BY T. GURNETT	FB 06 JAN 99
A	CHANGED MINIMUM DIMENSION "C" WAS; 0.94MM (0.037IN). DELETED DIMENSION H FROM DOCUMENT.	FB 07 APR 00