

ON Semiconductor

Is Now



To learn more about onsemi™, please visit our website at
www.onsemi.com

onsemi and onsemi. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that onsemi was negligent regarding the design or manufacture of the part. onsemi is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner. Other names and brands may be claimed as the property of others.

Improving the Versatility of the NLSF595 by Multiplexing

Prepared by: Fred Zlotnick
ON Semiconductor



ON Semiconductor®

<http://onsemi.com>

APPLICATION NOTE

The NLSF595 is basically a shift-register with serial inputs and parallel outputs, along with an RCK (pos. edge) and an OE (low) pin. The standard mode of operation involves loading in an 8 bit word by shifting in data followed by clock, either in software or through an SPI port. After the 8 bit word is loaded in, a positive rising edge is asserted on the RCK pin, and data is latched and held until this sequence is performed again. It is assumed that the OE pin is low. The output is now free to drive up to 8 LED segments, each segment must be ≤ 25 mA (sink only). The output is Over-Voltage Tolerant (OVT) and can accept any voltage level ≤ 7.0 volts. Since LEDs drop at least 1.5 V, the safe open circuit voltage to drive the diodes is 8.0 V. A series limiting resistor is then placed in each leg.

Multiplexing can achieve superior brightness with the same average current. J. Lepkowski et al¹ showed this in an application note. Other reasons for using multiplexing is to achieve more colors, or more levels of brightness of the LEDs. In the first scenario, the brightness is fixed by the supply voltage and the value of the limiting resistor used (along with the LED itself). By multiplexing, the designer can increase the brightness for a given level of current

consumption, or similarly reduce the current to achieve the same brightness. This design note will outline two approaches to multiplexing.

Method 1: All LEDs are affected the same.

In this method, the designer uses the OE pin to control the brightness. He sets the brightness to the maximum level and then uses an effective PWM technique to control the brightness. In both methods, the author will assume a 70 Hz refresh rate. This rate was chosen empirically to be high enough not to see the flicker, and not interfere with either 50 or 60 Hz lighting. The method is simple. The software designer creates a 14 ms routine and breaks it up into N sub-periods. The author will assume 4 sub-periods for convenience. This paper will show 5 conditions: OFF, 1/4 Brightness, 1/2 Brightness, 3/4 Brightness, Full Brightness. The OE pin is held HIGH for all four periods and that creates an OFF condition. Similarly, if the OE is held HIGH for 2 of the 4 periods, and LOW for 2 periods, the output is at 1/2 brightness. If the software engineer were trying to go from full brightness to OFF in graceful steps, he could use 10 periods, and go from full ON to full OFF in 140 ms. Similarly, he could chose 280, 560, or 1120 ms.

1. AND8067/D <http://www.onsemi.com/pub/Collateral/AND8067-D.PDF>




Figure 1. Output OE Pin for 1/2 Brightness

Method 2: Leave the $\overline{OE}$ pin fixed and create 3.5 ms periods that the software designer uses to update the data every time.

Case A: Output is to remain constant.

1. Either skip the shift routine or;
2. Shift the same data out and latch it in as above.

Case B: Output is to change either intensity or color.

Using the 3.5 ms period, pick one of 5 possible levels:

1. Full Brightness: Shift a ZERO to each line that is desired ON.

Keep the data the same for each of the 4 periods.

2. 3/4 Brightness: Shift a ZERO for 3 periods and a ONE for 1 period.
3. 1/2 Brightness: Shift a ZERO for two periods and a ONE for 2 Periods.
4. 1/4 Brightness: Shift a ZERO for 1 period and a ONE for 3 periods.
5. OFF: Shift a ONE for 4 periods.

Conclusion

Multiplexing can add to the versatility of the NLSF595 at no additional cost and very little software overhead, just a few bytes every 3.5 ms. Either the efficiency can improve or the number of colors may be enhanced or the ability to go from full on to full off gracefully can be achieved. It is also possible to create more colors by using different levels of brightness which will create more colors in a tri-color LED. All this is achieved at no extra hardware or system cost.

ON Semiconductor and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer.

PUBLICATION ORDERING INFORMATION

Literature Fulfillment:

Literature Distribution Center for ON Semiconductor
P.O. Box 5163, Denver, Colorado 80217 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
Email: ONlit@hibbertco.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada

JAPAN: ON Semiconductor, Japan Customer Focus Center
2-9-1 Kamimeguro, Meguro-ku, Tokyo, Japan 153-0051

Phone: 81-3-5773-3850

Email: r14525@onsemi.com

ON Semiconductor Website: <http://onsemi.com>

For additional information, please contact your local Sales Representative.