

Product Overview

NCP160: LDO Regulator, 250 mA, Ultra-High PSRR, Ultra-Low Noise

For complete documentation, see the data sheet.



The NCP160 is a linear regulator capable of supplying 250 mA output current. Designed to meet the requirements of RF and analog circuits, the NCP160 device provides low noise, high PSRR, low quiescent current, and very good load/line transients. The device is designed to work with a 1 μ F input and a 1 μ F output ceramic capacitor. It is available in two thickness ultra-small 0.35P, 0.64 mm x 0.64 mm Chip Scale Package (CSP) and XDFN-4 0.65P, 1 mm x 1 mm packages.

Similar Products:

	NCP160	NCP161	NCP163	NCP167
Output Current (A)	0.25	0.45	0.25	0.70
PSRR $f=1$ kHz (dB)	98	98	92	85
Dropout Voltage (V)	0.080	0.150	0.080	0.210

Features

- Ultra High PSRR 98dB at 1kHz, 48dB at 100kHz
- Ultra Low Output Noise 10 μ VRMS
- Ultra Low Quiescent current 18 μ A
- Operating Input Voltage Range 1.9V to 5.5V
- Very Low Dropout 80mV at 250mA
- Available in CSP4 0.35P and XDFN4 0.65P packages

Applications

- A/D and D/A Converters Power supply
- Audio codec
- Battery Powered Equipment
- Camera module
- Precision Analog Circuits

Benefits

- Excellent for power sensitive device like Wi-Fi module
- Very well suited for noise sensitive application
- Improved efficiency during light load conditions
- Suitable for battery powered device
- Low power dissipation at full load
- Great for space constrains application

End Products

- Cameras and camcoders
- Smartphones
- Tablets
- Wireless Routers

Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	Output	Polarity	V _O (V)	I _{O Typ} (A)	V _{I Min} (V)	V _{I Max} (V)	V _{DO Typ} (V)	I _{Q Typ} (mA)	PSR R (dB)	Noise (μV _{rms})	Enable	Power Good	Application	Package Type
NCP160AFCS180T2G	0.0697	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	1.8	0.25	1.9	5.5	0.18	0.018	98	10	Yes	No	Consumer	WLCSP-4
NCP160AFCS250T2G	0.0697	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	2.5	0.25	1.9	5.5	0.11	0.018	98	10	Yes	No	Consumer	WLCSP-4
NCP160AFCS270T2G	0.0697	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	2.7	0.25	1.9	5.5	0.1	0.018	90	10	Yes	No	Consumer	WLCSP-4
NCP160AFCS280T2G	0.0697	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	2.8	0.25	1.9	5.5	0.095	0.018	98	10	Yes	No	Consumer	WLCSP-4
NCP160AFCS285T2G	0.0697	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	2.85	0.25	1.9	5.5	0.095	0.018	98	10	Yes	No	Consumer	WLCSP-4
NCP160AFCS2925T2G	0.0697	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	2.925	0.25	1.9	5.5	0.09	0.018	98	10	Yes	No	Consumer	WLCSP-4
NCP160AFCS300T2G	0.0697	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	3	0.25	1.9	5.5	0.09	0.018	98	10	Yes	No	Consumer	WLCSP-4
NCP160AFCS320T2G	0.0697	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	3.2	0.25	1.9	5.5	0.085	0.018	98	10	Yes	No	Consumer	WLCSP-4
NCP160AFCS330T2G	0.0697	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	3.3	0.25	1.9	5.5	0.08	0.018	98	10	Yes	No	Consumer	WLCSP-4
NCP160AFCS350T2G	0.0697	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	3.5	0.25	1.9	5.5	0.075	0.018	98	10	Yes	No	Consumer	WLCSP-4
NCP160AFCS370T2G	0.0697	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	3.7	0.25	1.9	5.5	0.075	0.018	98	10	Yes	No	Consumer	WLCSP-4
NCP160AFCS450T2G	0.0697	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	4.5	0.25	1.9	5.5	0.065	0.018	98	10	Yes	No	Consumer	WLCSP-4
NCP160AFCS500T2G	0.0697	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	5	0.25	1.9	5.5	0.06	0.018	98	10	Yes	No	Consumer	WLCSP-4
NCP160AFCS514T2G	0.0697	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	5.14	0.25	1.9	5.5	0.06	0.018	98	10	Yes	No	Consumer	WLCSP-4
NCP160AFCS280T2G	0.0697	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	2.8	0.25	1.9	5.5	0.095	0.018	98	10	Yes	No	Consumer	WLCSP-4
NCP160AFCT180T2G	0.0635	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	1.8	0.25	1.9	5.5	0.18	0.018	98	10	Yes	No	Consumer	WLCSP-4

NCP160AFCT250T2G	0.0635	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	2.5	0.25	1.9	5.5	0.11	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160AFCT280T2G	0.0635	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	2.8	0.25	1.9	5.5	0.095	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160AFCT285T2G	0.0635	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	2.85	0.25	1.9	5.5	0.095	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160AFCT300T2G	0.0635	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	3	0.25	1.9	5.5	0.09	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160AFCT330T2G	0.0635	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	3.3	0.25	1.9	5.5	0.08	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160AFCT350T2G	0.0635	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	3.5	0.25	1.9	5.5	0.075	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160AFCT450T2G	0.0635	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	4.5	0.25	1.9	5.5	0.065	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160AFCT500T2G	0.0635	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	5	0.25	1.9	5.5	0.06	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160AFCT514T2G	0.0635	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	5.14	0.25	1.9	5.5	0.06	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160AFCTC180T2G		Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	1.8	0.25	1.9	5.5	0.18	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160AFCTC330T2G	0.0635	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	3.3	0.25	1.9	5.5	0.08	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160AMX180TBG	0.0729	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	1.8	0.25	1.9	5.5	0.18	0.018	98	10	Yes	No	Consumer	XDF N-4
NCP160AMX1825TBG	0.0729	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	1.825	0.25	1.9	5.5	0.18	0.018	98	10	Yes	No	Consumer	XDF N-4
NCP160AMX250TBG	0.0729	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	2.5	0.25	1.9	5.5	0.11	0.018	98	10	Yes	No	Consumer	XDF N-4
NCP160AMX275TBG	0.0729	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	2.75	0.25	1.9	5.5	0.095	0.018	98	10	Yes	No	Consumer	XDF N-4
NCP160AMX280TBG	0.0704	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	2.8	0.25	1.9	5.5	0.095	0.018	98	10	Yes	No	Consumer	XDF N-4
NCP160AMX285TBG	0.0729	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	2.85	0.25	1.9	5.5	0.095	0.018	98	10	Yes	No	Consumer	XDF N-4

NCP160AMX290TBG	0.0729	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	2.9	0.25	1.9	5.5	0.095	0.018	98	10	Yes	No	Consumer	XDF N-4
NCP160AMX300TBG	0.0716	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	3	0.25	1.9	5.5	0.09	0.018	98	10	Yes	No	Consumer	XDF N-4
NCP160AMX310TBG	0.0729	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	3.1	0.25	1.9	5.5	0.087	0.018	98	10	Yes	No	Consumer	XDF N-4
NCP160AMX320TBG	0.0729	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	3.2	0.25	1.9	5.5	0.085	0.018	98	10	Yes	No	Consumer	XDF N-4
NCP160AMX330TBG	0.0728	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	3.3	0.25	1.9	5.5	0.08	0.018	98	10	Yes	No	Consumer	XDF N-4
NCP160AMX350TBG	0.0729	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	3.5	0.25	1.9	5.5	0.075	0.018	98	10	Yes	No	Consumer	XDF N-4
NCP160AMX450TBG	0.0729	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	4.5	0.25	1.9	5.5	0.065	0.018	98	10	Yes	No	Consumer	XDF N-4
NCP160AMX500TBG	0.0729	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	5	0.25	1.9	5.5	0.06	0.018	98	10	Yes	No	Consumer	XDF N-4
NCP160AMX514TBG	0.0729	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	5.14	0.25	1.9	5.5	0.06	0.018	98	10	Yes	No	Consumer	XDF N-4
NCP160BFCS180T2G	0.0697	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	1.8	0.25	1.9	5.5	0.18	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160BFCS250T2G	0.0697	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	2.5	0.25	1.9	5.5	0.11	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160BFCS280T2G	0.0697	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	2.8	0.25	1.9	5.5	0.095	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160BFCS285T2G	0.0697	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	2.85	0.25	1.9	5.5	0.095	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160BFCS2925T2G	0.0697	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	2.925	0.25	1.9	5.5	0.09	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160BFCS300T2G	0.0697	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	3	0.25	1.9	5.5	0.09	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160BFCS330T2G	0.0697	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	3.3	0.25	1.9	5.5	0.08	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160BFCS350T2G	0.0697	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	3.5	0.25	1.9	5.5	0.075	0.018	98	10	Yes	No	Consumer	WLC SP-4

NCP160BFCS450T2G	0.0697	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	4.5	0.25	1.9	5.5	0.065	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160BFCS500T2G	0.0697	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	5	0.25	1.9	5.5	0.06	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160BFCS514T2G	0.0697	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	5.14	0.25	1.9	5.5	0.06	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160BFCT180T2G	0.0635	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	1.8	0.25	1.9	5.5	0.18	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160BFCT210T2G	0.0635	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	2.1	0.25	1.9	5.5	0.15	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160BFCT250T2G	0.0635	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	2.5	0.25	1.9	5.5	0.11	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160BFCT280T2G	0.0635	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	2.8	0.25	1.9	5.5	0.095	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160BFCT285T2G	0.0635	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	2.85	0.25	1.9	5.5	0.095	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160BFCT300T2G	0.0635	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	3	0.25	1.9	5.5	0.09	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160BFCT330T2G	0.0635	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	3.3	0.25	1.9	5.5	0.08	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160BFCT350T2G	0.0635	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	3.5	0.25	1.9	5.5	0.075	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160BFCT450T2G	0.0635	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	4.5	0.25	1.9	5.5	0.065	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160BFCT500T2G	0.0635	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	5	0.25	1.9	5.5	0.075	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160BFCT514T2G	0.0635	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	5.14	0.25	1.9	5.5	0.06	0.018	98	10	Yes	No	Consumer	WLC SP-4
NCP160BMX180TBG	0.0729	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	1.8	0.25	1.9	5.5	0.18	0.018	98	10	Yes	No	Consumer	XDF N-4
NCP160BMX1825TBG	0.0729	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	1.825	0.25	1.9	5.5	0.18	0.018	98	10	Yes	No	Consumer	XDF N-4
NCP160BMX250TBG	0.0729	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	2.5	0.25	1.9	5.5	0.11	0.018	98	10	Yes	No	Consumer	XDF N-4

NCP160BMX275TBG	0.0729	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	2.75	0.25	1.9	5.5	0.095	0.018	98	10	Yes	No	Consumer	XDF N-4
NCP160BMX280TBG	0.0729	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	2.8	0.25	1.9	5.5	0.095	0.018	98	10	Yes	No	Consumer	XDF N-4
NCP160BMX285TBG	0.0729	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	2.85	0.25	1.9	5.5	0.095	0.018	98	10	Yes	No	Consumer	XDF N-4
NCP160BMX300TBG	0.0729	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	3	0.25	1.9	5.5	0.09	0.018	98	10	Yes	No	Consumer	XDF N-4
NCP160BMX330TBG	0.0729	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	3.3	0.25	1.9	5.5	0.08	0.018	98	10	Yes	No	Consumer	XDF N-4
NCP160BMX350TBG	0.0729	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	3.5	0.25	1.9	5.5	0.075	0.018	98	10	Yes	No	Consumer	XDF N-4
NCP160BMX450TBG	0.0729	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	4.5	0.25	1.9	5.5	0.065	0.018	98	10	Yes	No	Consumer	XDF N-4
NCP160BMX500TBG	0.0729	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	5	0.25	1.9	5.5	0.06	0.018	98	10	Yes	No	Consumer	XDF N-4
NCP160BMX514TBG	0.0729	Pb-free Halide free non AEC-Q and PPAP	Active	Single	Positive	5.14	0.25	1.9	5.5	0.06	0.018	98	10	Yes	No	Consumer	XDF N-4

For more information please contact your local sales support at www.onsemi.com.

Created on: 11/26/2020