

AND9858/D

VCO Current Calibration for Optimal Synthesizer Phase Noise



ON Semiconductor®

www.onsemi.com

APPLICATION NOTE

Introduction

The phase noise of the AX5043 VCO depends on the setting of the parameter VCOI (register PLLVCOI). There is an optimum setting for each carrier frequency. The optimum setting of VCOI can vary from device to device and from application board to application board. Depending on the regulatory environment being targeted by an application, a constant setting of VCOI for all devices/boards during TX operation may not be good enough. For those cases we suggest to follow the VCOI calibration scheme that is described in this Application Note.

In summary, the calibration routine consists of finding the VCOI setting that results in a local minimum of the voltage at node FILT for the desired carrier frequency. The voltage at node FILT is measured with the AX5043's on-chip GPADC. To be able to run the calibration a connection on the application board from pin FILT to pin GPADC1 needs to be available. The calibration can be run using device mode TX_SYNTH, meaning that there is no spurious emission generated during calibration as the PA need not be active. It is not required to re-run calibration for each data transmission, as dependencies on VDD_IO and temperature are not significant, it must only be re-run if the carrier frequency is changed.

Hardware Prerequisites




Figure 1. Configuration for VCOI Calibration

Table 1. COMPONENT VALUES FOR 868 MHz OPERATION

Component	C1	C2	C3	C4
Value	39 pF	10 nF	10 nF not mandatory	12 kΩ

Calibration Procedure

1. Setup the device for CW transmission at the desired carrier frequency.
2. Setup for GPADC operation, for an 48 MHz reference clock this is:
Register 0xf34 = 0x81
3. Loop over VCOI values and take GPADC readings of the VCO control voltage for each VCOI setting:
 - a. Set the PLLVCOI register.
 - b. Set power mode TX_SYNTH, register PWRMODE = 0x0C.
 - c. Run the VCO ranging routine; if PLL cannot be ranged for this VCOI value then go to the next one.
 - d. Make the VCO control voltage available at device pin FILT, register PLLLOOP |= 0x04.
 - e. Trigger GPADC conversions and read the results; register GPADCCTRL = 0x84, wait for GPADCCTRL BUSY bit to clear; read GPADC13VALUE1 and GPADC13VALUE0.

A suggestion is to run 100 – 1000 dummy conversions and then use the mean of the next 20 conversions.

- f. Set PLLLOOP back to its original value.
4. Find the local minimum in the GPADC readings, use the corresponding VCOI value for all RX and TX operation at this carrier frequency. Care must be taken to avoid mistaking a VCO range boundary as a local minimum, see the graphs in the next chapter.

Example Results

In the following adjacent channel power measurements for two application boards are shown along with the corresponding VCOI calibration data. It can be seen that the optimum adjacent channel power is obtained where the VFILT has a local minimum. The VCOI calibration outlined in this Application Note is an algorithm to find the VCOI at the VFILT local minimum by measuring the VFILT values using the GPADC.

Jumps that can be seen both in the adjacent channel measurements and in the calibration data are caused by VCO range changes. The internal VCO auto ranging was run for each VCOI setting. In a microcontroller implementation of the local minimum search care has to be taken to avoid mistaking a range boundary for a local minimum.

AND9858/D

**BD#2, 868.3 MHz, CW, 25 kHz channels, internal VCO,
Pout = 13.2 dBm**




Figure 2. Adjacent Channel Power vs. VCOI for Board #3

**BD#3, 868.3 MHz, CW, 25 kHz channels, internal VCO,
VCOI Calibration Data**




Figure 3. VFILT Value Measured with the GPADC vs. VCOI for Board #3, the Local Minimum can be seen at VCOI = 26, a VCO Range Boundary can be seen at VCOI = 59

AND9858/D

BD#2, 868.3 MHz, CW, 25 kHz channels, internal VCO,
Pout = 13.2 dBm




Figure 4. Adjacent Channel Power vs. VCOI for Board #2

BD#2, 868.3 MHz, CW, 25 kHz channels, internal VCO,
VCOI Calibration Data




Figure 5. VFILT Value Measured with the GPADC vs. VCOI for Board #2,
the Local Minimum can be seen at VCOI = 24,
VCO Range Boundaries can be seen at VCOI = 45 and VCOI = 60

AND9858/D

Implementation in AX–RadioLab

The VCOI calibration procedure described above has been implemented in AX–RadioLab for AX5043, AX8052F143, and AXM0F243 development kits. The calibration algorithm can be found in the `axradio_init()`

function of `easyAX5043.c`. By default, this is disabled, but can be easily enabled in the Pin Configuration panel of AX–RadioLab by selecting “VCO Calibration” in the “VCO Cal Config” field.





Figure 6.

ON Semiconductor and  are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor
19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free
USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910

ON Semiconductor Website: www.onsemi.com

Order Literature: <http://www.onsemi.com/orderlit>

For additional information, please contact your local Sales Representative