

Product Overview

NCV7707: Door Module Driver

For complete documentation, see the data sheet.

The NCV7707 is a powerful driver for automotive body control systems. The device is designed to control several loads in the front foor of a vehicle. The monolithic IC is able to control mirror functions like mirror positioning, heating and folding including the electro-chromic mirror feature. Besides two half-bridge outputs to control lock and safe-lock motors, the device features four high-side outputs to drive LEDs or incandescent bulbs (up to 10W). To allow maximum flexibility, all lighting outputs can be PWM controlled thru PWM inputs (external signal source) or by an internal programmable PWM generator unit. The NCV7707 is controlled thru a 24 bit SPI interface with in-frame response.

Features

- Operating Range from 5.5 V to 28 V
- Six HighSide and Six LowSide Drivers Connected as HalfBridges
- Four HighSide Lamp Drivers
- One HighSide Driver for Mirror Heating
- Electro Chromic Mirror Control
- Independent PWM Functionality for All Outputs
- Integrated Programmable PWM Generator Unit for All Lamp Driver Outputs
- Programmable Softstart Function to Drive Loads with Higher Inrush Currents as Current Limitation Value
- Multiplex Current Sense Analog Output for Advanced Load Monitoring
- Very Low Current Consumption in Standby Mode

For more features, see the data sheet

Applications

- Decentralized Door Electronic Systems
- Body Control Units (BCUs)

End Products

- Automobiles

Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	Number of Drivers	V _{CC} Max (V)	V _{(BR)GSS} Max (V)	V _{(BR)DSS} Max (V)	I _D Max (A)	r _{DS(on)} Max (Ω)	T _J Max (°C)	Package Type
NCV7707DQR2G		AEC Qualified PPAP Capable Pb-free Halide free	Active	12	28	5.5	40	-	3	150	SSOP-36 EP

For more information please contact your local sales support at www.onsemi.com.

Created on: 4/5/2020