

Product Overview

LV8761V: Motor Driver, H-Bridge, Forward / Reverse

For complete documentation, see the data sheet.

The LV8761V is an H-bridge driver that can control four operation modes (forward, reverse, brake, and standby) of a motor. The low on-resistance, zero standby current, highly efficient IC is optimal for use in driving brushed DC motors for office equipment.

Features

- Built-in current limiter circuit
- Built-in thermal protection circuit
- Built-in short-circuit protection function
- Short-circuit protection circuit selectable from latch-type or auto reset-type
- Low ON Resistance: 0.52Ω
- Stand-by Current: $0\mu\text{A}$
- TSSOP20J Package
- Forward/reverse H-bridge motor driver: 1 channel
- Unusual condition warning output pin
- Output Current : 3A

For more features, see the data sheet

Benefits

- Current Protection
- Thermal Protection
- Short Protection
- Safety Design
- (Upper and Lower Total), High Efficiency
- Low Consumption
- Small Design Footprint

Applications

- Brush DC Motors
- Computing & Peripherals
- Industrial

End Products

- Flatbed Scanner
- Inkjet Printer
- Multi-Function Printer
- Document Scanner
- Cash Machine

Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	V _M Min (V)	V _M Max (V)	V _{CC} Min (V)	V _{CC} Max (V)	I _O Min (A)	I _O Peak Max (A)	Control Type	Current Sense	Package Type
LV8761V-TLM-E	2.1599	Pb-free non AEC-Q and PPAP	Active	9	35	3	6	3	4	Parallel	External Resistor	SSOP-36J EP

For more information please contact your local sales support at www.onsemi.com.

Created on: 12/3/2020