

Product Overview

LV8712T: Stepping Motor Driver, Constant-Current Control, PWM

For complete documentation, see the data sheet.

The LV8712T is a microstepping motor driver with built-in translator for easy operation. It supports full-step, half-step, quarter-step, and 1/8-step resolution. The LV8712T is optimal for driving stepping motors of scanners and small printers.

Features

- Excitation mode can be set to 2-phase, 1-2 phase, W1-2 phase, or 2W1-2 phase
- Microstep can control easily by the CLK-IN input.
- Output ON resistance RON = 1.1 (upper and lower total, typical, Ta = 25C)
- Stand-by Current: 0uA
- TSSOP24 Package
- Single-channel PWM constant-current control stepping motor driver incorporated.
- Power-supply voltage of motor VM max = 18V
- Output current IO max = 0.8A
- A thermal shutdown circuit and a low voltage detecting circuit are built into.

Benefits

- Various Step Adjustment Available
- Easy control
- High Efficiency
- Low Consumption
- Small Design

Applications

- Stepper Motors
- Computing & Peripherals
- Industrial

End Products

- Point-of-Sale Printers
- Flatbed Scanner
- Document Scanner
- PoE Point of Sales Terminal
- PoE Security Camera

Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	VM Min (V)	VM Max (V)	VCC Min (V)	VCC Max (V)	IO Max (A)	IO Peak Max (A)	Step Resolution	Control Type	Current Sense	Fault Detection	Package Type
LV8712T-TLM-H	1.228	Pb-free Halide free non AEC-Q and PPAP	Active	4	16	2.7	5.5	0.8	1	¼	Clock	External Resistor	Thermal UVLO	TSSOP-24

For more information please contact your local sales support at www.onsemi.com.

Created on: 11/27/2020