**ON Semiconductor** 

Is Now

# Onsemi

To learn more about onsemi<sup>™</sup>, please visit our website at <u>www.onsemi.com</u>

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product factures, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and asfety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or by customer's technical experts. onsemi products and actal performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiari

# High Voltage Transistors NPN Silicon

#### Features

• Pb-Free Package is Available\*

#### MAXIMUM RATINGS

Rating	Symbol	BF420	BF422	Unit
Collector – Emitter Voltage	V <sub>CEO</sub>	300	250	Vdc
Collector-Base Voltage	V <sub>CBO</sub>	300	250	Vdc
Emitter-Base Voltage	V <sub>EBO</sub>	5.	.0	Vdc
Collector Current – Continuous	۱ <sub>C</sub>	5	0	mAdc
Collector Current – Peak	I <sub>CM</sub>	10	00	mA
Total Device Dissipation (Note 1) @ T <sub>A</sub> = 25°C Derate above 25°C	P <sub>D</sub>	83 6		mW mW/°C
Operating and Storage Junction Temperature Range	T <sub>J</sub> , T <sub>stg</sub>	–55 to	o +150	°C

#### THERMAL CHARACTERISTICS

Characteristic	Symbol	Max	Unit
Thermal Resistance, Junction–to–Ambient	$R_{\theta JA}$	150	°C/W
Thermal Resistance, Junction-to-Lead	$R_{\theta JL}$	68	°C/W


Maximum ratings are those values beyond which device damage can occur. Maximum ratings applied to the device are individual stress limit values (not normal operating conditions) and are not valid simultaneously. If these limits are exceeded, device functional operation is not implied, damage may occur and reliability may be affected.


1. Mounted on a FR4 board with 200 mm<sup>2</sup> of 1 oz copper and lead length of 5 mm.



### **ON Semiconductor®**

http://onsemi.com





#### **ORDERING INFORMATION**

Device	Package	Shipping <sup>†</sup>			
BF420ZL1	TO-92	2000/Ammo Box			
BF420ZL1G	TO–92 (Pb–Free)	2000/Ammo Box			
BF422	TO-92	5000 Units/Box			
BF422G	TO-92 (Pb-Free)	5000 Units/Box			
BF422RL1	TO-92	2000/Tape & Reel			
BF422RL1G	TO–92 (Pb–Free)	2000/Tape & Reel			
BF422ZL1	TO-92	2000/Ammo Pack			
BF422ZL1G	TO–92 (Pb–Free)	2000/Ammo Pack			

\*For additional information on our Pb–Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

# BF420, BF422

## **ELECTRICAL CHARACTERISTICS** (T<sub>A</sub> = 25°C unless otherwise noted)

Characteristic		Symbol	Min	Мах	Unit	
OFF CHARACTERISTICS						
Collector – Emitter Breakdown Voltage (Note 1) ( $I_C = 1.0 \text{ mAdc}, I_B = 0$ )	BF420 BF422	V <sub>(BR)CEO</sub>	300 250		Vdc	
Collector – Base Breakdown Voltage ( $I_C = 100 \ \mu Adc, I_E = 0$ )	BF420 BF422	V <sub>(BR)CBO</sub>	300 250		Vdc	
Emitter – Base Breakdown Voltage ( $I_E = 100 \ \mu Adc, I_C = 0$ )	BF420 BF422	V <sub>(BR)EBO</sub>	5.0 5.0		Vdc	
Collector Cutoff Current ( $V_{CB} = 200 \text{ Vdc}, I_E = 0$ )	BF420 BF422	I <sub>CBO</sub>		0.01	μAdc	
Emitter Cutoff Current ( $V_{EB} = 5.0 \text{ Vdc}, I_C = 0$ )	BF420 BF422	I <sub>EBO</sub>		100 -	nAdc	
ON CHARACTERISTICS						
DC Current Gain (I <sub>C</sub> = 25 mAdc, V <sub>CE</sub> = 20 Vdc)	BF420 BF422	h <sub>FE</sub>	50 50		-	
Collector – Emitter Saturation Voltage ( $I_C = 20 \text{ mAdc}, I_B = 2.0 \text{ mAdc}$ )		V <sub>CE(sat)</sub>	_	0.5	Vdc	
Base – Emitter Saturation Voltage ( $I_C = 20 \text{ mAdc}, I_B = 2.0 \text{ mAdc}$ )		V <sub>BE(sat)</sub>	-	2.0	Vdc	
SMALL-SIGNAL CHARACTERISTICS					•	

Current Gain – Bandwidth Product (I <sub>C</sub> = 10 mAdc, V <sub>CE</sub> = 10 Vdc, f = 20 MHz)	f <sub>T</sub>	60	-	MHz
Common Emitter Feedback Capacitance ( $V_{CB} = 30 \text{ Vdc}, I_E = 0, f = 1.0 \text{ MHz}$ )	C <sub>re</sub>	-	1.6	pF

1. Pulse Test: Pulse Width  $\leq$  300 µs; Duty Cycle  $\leq$  2.0%.





Figure 4. "ON" Voltages

#### PACKAGE DIMENSIONS

TO-92 (TO-226) CASE 029-11 **ISSUE AL** 



NOTES 1.

- DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982. CONTROLLING DIMENSION: INCH.
- 2. 3.
- CONTOUR OF PACKAGE BEYOND DIMENSION R IS UNCONTROLLED. 4.
- LEAD DIMENSION IS UNCONTROLLED IN P AND BEYOND DIMENSION K MINIMUM.

	INCHES		MILLIM	ETERS
DIM	MIN	MAX	MIN	MAX
Α	0.175	0.205	4.45	5.20
В	0.170	0.210	4.32	5.33
С	0.125	0.165	3.18	4.19
D	0.016	0.021	0.407	0.533
G	0.045	0.055	1.15	1.39
Н	0.095	0.105	2.42	2.66
J	0.015	0.020	0.39	0.50
K	0.500		12.70	
L	0.250		6.35	
N	0.080	0.105	2.04	2.66
Р		0.100		2.54
R	0.115		2.93	
٧	0.135		3.43	

STYLE 14: PIN 1. EMITTER

2. COLLECTOR

3. BASE

ON Semiconductor and 💷 are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC products are not designed, intended, or authorized for use a components in systems intended for surgical implant into the body, or other applications and actual performance may liability of the second to the second intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, ad distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, and claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 61312, Phoenix, Arizona 85082-1312 USA Phone: 480-829-7710 or 800-344-3860 Toll Free USA/Canada Fax: 480-829-7709 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada

Japan: ON Semiconductor, Japan Customer Focus Center 2-9-1 Kamimeguro, Meguro-ku, Tokyo, Japan 153-0051 Phone: 81-3-5773-3850

ON Semiconductor Website: http://onsemi.com

Order Literature: http://www.onsemi.com/litorder

For additional information, please contact your local Sales Representative.