

Product Overview

AP0200AT: Image Signal Processor, 2 MP

For complete documentation, see the data sheet.

AP0200AT is a dedicated automotive image co-processor that enables flexible camera platforms using high performance ON Semiconductor megapixel high dynamic range (HDR) sensors. The two-chip solution of sensor and co-processor allows for multiple camera price and performance points with re-use of circuit board design, fast time to market and design flexibility. Sensor performance is enhanced by the reduction in heat resulting from a separate co-processor chip while at the same time enabling high performance features. The AP0200AT offers Ethernet output and supports up to 2 Megapixel sensors. It includes a spatial transfer engine that works with up to 1.2 MP sensors and offers 185-degree fisheye lens distortion correction, perspective correction and multiple view options such as split side view, triptych and trailer hitch. This co-processor works with ON Semiconductor's AR0230AT, AR0132AT, AR0140AT and AR0136AT HDR automotive sensors, and is ideal for Ethernet rear view cameras.

Features

- HDR
- Ethernet

Applications

- Automotive

Part Electrical Specifications								
Product	Pricing (\$/Unit)	Compliance	Status	Frame Rate (fps)	Video	Output Format	Compatible Sensors	Package Type
AP0200AT2L00XEGA 0-DR		AEC Qualified	Active	30	1080p/30 fps	H.264	AR0140AT	VFPGA-100
		PPAP Capable			960p/45 fps	MJPEG	AR0230AT	
		Pb-free			720p/60 fps		AR0132AT	
		Halide free					AR0136AT	
AP0200AT2L00XEGA 0-DR1		AEC Qualified	Active	30	720p/60 fps	H.264	AR0230AT	VFPGA-100
		PPAP Capable			960p/45 fps	MJPEG	AR0136AT	
		Pb-free			1080p/30 fps		AR0132AT	
		Halide free					AR0140AT	
AP0200AT2L00XEGA 0-TR		AEC Qualified	Active	30	960p/45 fps	MJPEG	AR0136AT	VFPGA-100
		PPAP Capable			720p/60 fps	H.264	AR0230AT	
		Pb-free			1080p/30 fps		AR0140AT	
		Halide free					AR0132AT	

For more information please contact your local sales support at www.onsemi.com.

Created on: 7/15/2020