

Product Overview

PYTHON25K: CMOS Image Sensor, 26.2 MP, Global Shutter

For complete documentation, see the data sheet.

The PYTHON 25K is a 26.2 MP (5120 x 5120 pixel) 10-bit CMOS image sensor in APS-H optical format, supporting up to 80 frame per second readout at full resolution.

High sensitivity 4.5 μm pixels support both pipelined and triggered global shutter readout modes. The sensor also supports correlated double sampling (CDS) readout in global shutter mode, reducing noise and increasing dynamic range.

The sensor is programmed using a four-wire serial peripheral interface. Black level can be calibrated automatically, or adjusted using a user programmable offset. The sensor also supports readout of up to 32 separate regions of interest (ROI) to increase frame rate. Image data is accessed through 32, 16, 8, or 4 LVDS channels, each running at 720 Mbps, and a separate synchronization channel is provided to facilitate image reconstruction.

The PYTHON 25K is packaged in a 355-pin μPGA package and is available in a monochrome, Bayer color, and extended near-infrared (NIR) configurations.

Features

- IP-CDS global shutter technology
- HW scalable family
- High configurability
- Fast adaptability
- Multiple windowing
- High frame rate

Applications

- Image Capture

Benefits

- Global shutter imaging with single digit noise performance
- One camera design to support multiple resolutions
- High flexibility to optimize sensor for end application
- Fast switching between operating modes
- Speed increase from windowing in x- and y- direction
- Fast image capture capabilities

End Products

- Machine Vision camera
- Industrial cameras and systems
- intelligent Transportation Systems (ITS)
- Inspection system (food, bottles, recycling labels, etc.)
- Medical Imaging system

Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	Type	Megapixels	Frame Rate (fps)	Optical Format	Shutter Type	Pixel Size (μm)	Output Interface	Color	Package Type
NOICPSN025KA-GTI		Pb-free Halide free non AEC-Q and PPAP	Active	CMOS	26.2	80	APS-H	Pipelined and Triggered Global	4.5 x 4.5	LVDS		CPGA-355
NOIP1FN025KA-GTI		Pb-free Halide free non AEC-Q and PPAP	Active	CMOS	26.2	80	APS-H	Pipelined and Triggered Global	4.5 x 4.5	LVDS	NIR	CPGA-355
NOIP1SE025KA-GTI		Pb-free Halide free non AEC-Q and PPAP	Active	CMOS	26.2	80	APS-H	Pipelined and Triggered Global	4.5 x 4.5	LVDS	Bayer Color	CPGA-355
NOIP1SN025KA-GTI		Pb-free Halide free non AEC-Q and PPAP	Active	CMOS	26.2	80	APS-H	Pipelined and Triggered Global	4.5 x 4.5	LVDS	Mono	CPGA-355

For more information please contact your local sales support at www.onsemi.com.

Created on: 10/28/2020