

## Product Overview

### C-SERIES SiPM: Silicon Photomultiplier Sensors, C-Series (SiPM)

For complete documentation, see the data sheet.

ON Semiconductor's C-Series silicon photomultiplier (SiPM) sensors feature industry-leading low dark count rates of 30 kHz/mm<sup>2</sup>, in combination with exceptional breakdown voltage uniformity of  $\pm 250$  mV. The high photon detection efficiency (PDE) extends far into the blue part of the spectrum using a high-volume, CMOS process.

C-Series sensors are available in 1 mm, 3 mm and 6 mm sizes and a variety of microcell sizes. They are packaged in a tileable molded lead frame (MLP) package that is compatible with industry standard, lead-free, reflow soldering processes. C-Series also feature a unique fast output for fast timing applications.

#### Features

- >40% PDE at 420 nm, and extended sensitivity to 300 nm for improved UV sensitivity
- Ultra-low dark count rates of 30 kHz/mm<sup>2</sup>
- Exceptional breakdown voltage uniformity of  $\pm 250$  mV over all C-Series products
- Temperature stability of 21.5 mV/°C
- Ultra-fast rise times of 300 ps with 600 ps pulse width from a unique 'fast output' terminal
- Bias voltage of <30 V
- 1 mm, 3 mm, and 6 mm sensor sizes

#### Benefits

- Solid state alternative to the legacy PMT for a wide range of applications
- High gain of  $10^6$  leads to single photon sensitivity
- Best V<sub>br</sub> uniformity in the industry
- Compact, robust packaging
- Evaluation boards with either SMA connectors or pins are available for easy evaluation

#### Applications

- Medical Imaging
- Hazard & Threat
- 3D Ranging & Sensing
- Biophotonics & Sciences
- High Energy Physics

## Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	Type	Array Format	Active Area Dimensions	Microcell Size (µm)	Optimized Wavelength (nm)	PDE @ Max Overvoltage (%)	DCR @ Typical Overvoltage (KHz/mm <sup>2</sup> )	Package Type
MICROFC-10010-SMT-TR		Pb-free Halide free non AEC-Q and PPAP	Active	Single		1 mm x 1 mm	10	420	18	30	CWDFN-4
MICROFC-10010-SMT-TR1		Pb-free Halide free non AEC-Q and PPAP	Active	Single		1 mm x 1 mm	10	420	18	30	CWDFN-4
MICROFC-10020-SMT-TR		Pb-free Halide free non AEC-Q and PPAP	Active	Single		1 mm x 1 mm	20	420	31	30	CWDFN-4
MICROFC-10020-SMT-TR1		Pb-free Halide free non AEC-Q and PPAP	Active	Single		1 mm x 1 mm	20	420	31	30	CWDFN-4
MICROFC-10035-SMT-TR		Pb-free Halide free non AEC-Q and PPAP	Active	Single		1 mm x 1 mm	35	420	41	30	CWDFN-4
MICROFC-10035-SMT-TR1		Pb-free Halide free non AEC-Q and PPAP	Active	Single		1 mm x 1 mm	35	420	41	30	CWDFN-4
MICROFC-30020-SMT-TR		Pb-free Halide free non AEC-Q and PPAP	Active	Single		3 mm x 3 mm	20	420	31	30	CWDFN-4
MICROFC-30020-SMT-TR1		Pb-free Halide free non AEC-Q and PPAP	Active	Single		3 mm x 3 mm	20	420	31	30	CWDFN-4
MICROFC-30035-SMT-TR		Pb-free Halide free non AEC-Q and PPAP	Active	Single		3 mm x 3 mm	35	420	41	30	CWDFN-4
MICROFC-30035-SMT-TR1		Pb-free Halide free non AEC-Q and PPAP	Active	Single		3 mm x 3 mm	35	420	41	30	CWDFN-4
MICROFC-30050-SMT-TR		Pb-free Halide free non AEC-Q and PPAP	Active	Single		3 mm x 3 mm	50	420	47	30	CWDFN-4
MICROFC-30050-SMT-TR1		Pb-free Halide free non AEC-Q and PPAP	Active	Single		3 mm x 3 mm	50	420	47	30	CWDFN-4
MICROFC-60035-SMT-TR		Pb-free Halide free non AEC-Q and PPAP	Active	Single		6 mm x 6 mm	35	420	41	30	CWDFN-4

MICROFC-60035-  
SMT-TR1

Pb-free  
Halide free  
non AEC-  
Q and  
PPAP

Active

Single

6 mm x 6  
mm

35

420

41

30

CWDFN-4

**For more information please contact your local sales support at [www.onsemi.com](http://www.onsemi.com).**

**Created on: 11/24/2020**