

Product Overview

MC74AC574: Octal D Flip-Flop with 3-State Outputs

For complete documentation, see the data sheet.

The MC74AC574/74ACT574 is a high-speed, low power octal flip-flop with a buffered common Clock (CP) and a buffered common Output Enable (OE). The information presented to the D inputs is stored in the flip-flops on the LOW-to-HIGH Clock (CP) transition. The MC74AC574/74ACT574 is functionally identical to the MC74AC374/ 74ACT374 except for the pinouts.

Features

- Inputs and Outputs on Opposite Sides of Package Allowing Easy Interface with Microprocessors
- Useful as Input or Output Port for Microprocessors
- Functionally Identical to MC74AC374/74ACT374
- 3-State Outputs for Bus-Oriented Applications
- Outputs Source/Sink 24 mA
- ACT574 Has TTL Compatible Inputs
- Pb-Free Packages are Available

Part Electrical Specifications

Product	Compliance	Status	Type	Channels	V _{CC} Min (V)	V _{CC} Max (V)	t _{pd} Max (ns)	I _O Max (mA)	Package Type
MC74AC574DTR2G	Pb-free	Active	D-Type	8	2	6	9.5	24	TSSOP-20
	Halide free								
MC74AC574DWG	Pb-free	Active	D-Type	8	2	6	9.5	24	SOIC-20W
	Halide free								
MC74AC574DWR2G	Pb-free	Active	D-Type	8	2	6	9.5	24	SOIC-20W
	Halide free								

For more information please contact your local sales support at www.onsemi.com.

Created on: 9/21/2019