

1.2 MP Smart iToF 1/3.2-inch Stacked BSI Global Shutter Depth Sensor AF0130, AF0131

onsemi AF0130 and AF0131 Smart Indirect Time of Flight (iToF) sensors are a 1/3.2-inch optical format, back side illuminated CMOS global shutter depth and imaging solution. The sensors have on-chip dual laser driver controls and modulation frequencies (up to 200 MHz) as well as on-chip laser eye-safety thresholds.


The AF0130 sensor version comes with a depth processing ASIC stacked below its pixel area which calculates depth, confidence and intensity maps at high speeds from its laser modulated exposures.

The AF0131 sensor version does not come with on-chip depth processing but does come with the same performance. This sensor is for solutions which prefer their own depth calculations off-chip.

Table 1. KEY PERFORMANCE PARAMETERS


Parameter	Typical Value
Optical Format	1/3.2 inch (5.60 mm, 4:3 Aspect Ratio)
Active Pixels	1280 (H) x 960 (V)
Pixel Size	3.5 x 3.5 μ m Back Side Illuminated (BSI)
Chief Ray Angle	30°
Shutter Type	Global Shutter
One-Time Programmable Memory (OTPM)	Three instances of 1024 x 24 bits
Input Clock Range	10–30 MHz
Interface	– Data: MIPI (2 Lanes, 2 Gbps/lane) – Host: Two-Wire / Four-Wire – Laser Driver: Three-Wire – Laser Modulation: LVDS
ADC Resolution	10–11 bit
Analog Gain Range	1–7.75x gain
Frame Rate	Mode 2.2: Max 60 fps (1.2 MP), 110 fps (VGA) Mode 3.2: Max 54 fps (VGA)
Read Noise	<6 e ⁻ with on-chip memory (C _{1:4}) <3 e ⁻ from storage gates (SG _{1:2})
Binning	2x2, 4x4
SNR _{MAX} (60 °C)	Mode 2.2: 46 dB (RAW), 52 dB (Intensity) Mode 3.2: 52 dB (RAW), 58 dB (Intensity)
Dynamic Range (60 °C)	Mode 2.2: 64 dB (RAW), 69 dB (Intensity) Mode 3.2: 67 dB (RAW), 72 dB (Intensity)
Supply Voltage I/O Digital Analog	1.2 V, 1.8 V, 2.8 V
Power Consumption (Note 1)	For 30 fps and 1 ms exposure: ~ 600 mW in Mode 2.2 (100 MHz) ~ 900 mW in Mode 3.2 (100+120 MHz)
Operating Temperature	–30 °C < T _J < +85 °C
Optimal Performance Temperature	0 °C < T _J < +60 °C
Package Options	– CSP (6.06 x 4.84 mm) 11x8 pin, 0.5 mm pitch – Bare Die
θ JA: °C/W (Note 2)	32.0
θ JB: °C/W	10.0

- Power consumption will increase with exposure time, frame rate and modulation frequency due to AVDD_MG supply.
- θ JA is dependent on the customer module design and should not be used for calculating junction temperature.



ODCSP87 6.05x4.83x0.63, 0.50P
CASE 570AZ

MARKING DIAGRAM



XXXX = Specific Device Code
Y = Year
W = Work Week
NNN = Serial Number

ORDERING INFORMATION

See detailed ordering and shipping information on page 2 of this data sheet.

Public Data Sheet

Interested in what you see? If you would like more detailed information, please request the full version of our data sheet.

[Request Full Data Sheet](#)

AF0130, AF0131

Features

- 1.2 MP CMOS Smart iToF Sensor with Advanced 3.5 μm Pixel Stacked BSI Technology
- Superior Low-Light and Ambient-Light Performance
- Enhanced NIR Response at 850 nm and 940 nm Wavelength (QE > 40%)
- Dual Laser (Frequency) Operation for Increased Depth Range (Disambiguation) in VGA Resolution
- Low Voltage Differential Signal (LVDS) Driver for Modulation Control of Two Lasers up to 200 MHz
- Two or Four-Wire Serial Interface for Register Access
- 2 Gbps/Lane, 2-lane MIPI CSI-2 D-PHY Data Interface
- Laser Eye Safety Monitoring
- Three Output Mode: RAW, Data Reduction (DR), Integrated Depth Processing (DP)
- Phase and Pulsed (Hybrid) Modulation Support
- Simultaneous Depth, Confidence and Grayscale Output
- Horizontal and Vertical Mirroring, Windowing and Pixel Binning
- Context State Machine with 64 Programmable Contexts

- Automatic Exposure Control (AEC)
- Pixel Identification & Correction (PDI & PDC)
- Multi Camera and Interference Mitigation
- Reduced Motion Artefacts due to Decoupling between Integration and Readout
- Hardware Trigger Control
- On-Chip Mean and Histogram Statistics for Smart Control
- On-Chip Temperature Sensor
- These Devices are Pb-Free and RoHS Compliant

Applications


- Computing
- Drones, Robotics & Automation
- Metrology
- Machine Vision
- Future Retail & Intelligent Logistics
- Security & Access Control
- Virtual or Augmented Reality
- 3D Modeling

Table 2. ORDERING INFORMATION – PART

Part Number	Container Qty	Product Description	On-chip Depth Processing	Protective Film
AF0130CSSM30SMKA1-CP	3000	AF0130 REV2 Production Samples (AF0131 + Depth, Confidence & Visual)	yes	yes
AF0130CSSM30SMKA1-CP2	50			
AF0131CSSM30SMKA1-CP	3000	AF0131 REV2 Production Samples (RAW, DR, 1.2 MP, 30° CRA)	no	yes
AF0131CSSM30SMKA1-CP2	50			
AF0130CSSM30SMKA1-CR	3000	AF0130 REV2 Production Samples (AF0131 + Depth, Confidence & Visual)	yes	no
AF0130CSSM30SMKA1-CR2	50			
AF0131CSSM30SMKA1-CR	3000	AF0131 REV2 Production Samples (RAW, DR, 1.2 MP, 30° CRA)	no	no
AF0131CSSM30SMKA1-CR2	50			





Table 3. ORDERING INFORMATION – EVALUATION BOARD

Part Number	Product Description
AF0130CSSM30SMKAH3-GEVK	AF0130 Sensor Headboard + Lens (940 nm filter, 65° HFOV)
AGBENECS-GEVK	Laser Headboard (4 VCSEL's, 60° HFOI)
AGB1N0CS-GEVK	Demo 3 Board (FPGA Base Board including USB Cable and Tripod)




ODCSP87 6.05x4.83x0.63, 0.50P
CASE 570AZ
ISSUE A


DATE 17 JUN 2024



DIM	MILLIMETERS		
	MIN.	NOM.	MAX.
A	---	---	0.762
A1	0.081	0.101	0.121
A2	0.631 REF.		
A3	0.425	0.440	0.455
A4	0.171	0.191	0.211
b	0.184	0.204	0.224
D	6.030	6.055	6.080
D1	4.480 REF.		
D2	2.956	2.981	3.006
E	4.810	4.835	4.860
E1	3.360 REF.		
E2	2.380	2.405	2.430
e	0.500 BSC		



GENERIC
MARKING DIAGRAM*



XXXX = Specific Device Code
Y = Year
W = Work Week
NNN = Serial Number

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "•", may or may not be present. Some products may not follow the Generic Marking.

RECOMMENDED MOUNTING FOOTPRINT*
*FOR ADDITIONAL INFORMATION ON OUR Pb-FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ONSEMI SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERM/D.

DOCUMENT NUMBER:	98AON62452H	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	ODCSP87 6.05x4.83x0.63, 0.50P	PAGE 1 OF 1

onsemi and Onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales