

MOSFET – N-Channel, Shielded Gate, POWER trench®

100 V, 18 A, 23 mΩ

FDMC86102L

General Description

This N-Channel MOSFET is produced using onsemi's advanced POWER trench process that incorporates Shielded Gate technology. This process has been optimized for the on-state resistance and yet maintain superior switching performance.

Features

- Shielded Gate MOSFET Technology
- Max $R_{DS(on)}$ = 23 mΩ at V_{GS} = 10 V, I_D = 7 A
- Max $R_{DS(on)}$ = 34 mΩ at V_{GS} = 4.5 V, I_D = 5.5 A
- Low Profile – 1 mm Max in Power 33
- Pb-Free, Halide Free and RoHS Compliant

Applications


- DC-DC Conversion

MAXIMUM RATINGS (T_A = 25°C unless otherwise noted)


Symbol	Parameter	Value	Unit
V_{DS}	Drain to Source Voltage	100	V
V_{GS}	Gate to Source Voltage	±20	V
I_D	Drain Current: Continuous, T_C = 25°C Continuous, T_A = 25°C (Note 1a) Pulsed	18 7 30	A
E_{AS}	Single Pulse Avalanche Energy (Note 3)	63	mJ
P_D	Power Dissipation: T_C = 25°C T_A = 25°C (Note 1a)	41 2.3	W
T_J, T_{STG}	Operating and Storage Junction Temperature Range	-55 to +150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

V_{DS}	$R_{DS(on)}$ MAX	I_D MAX
100 V	23 mΩ @ 10 V	18 A
	34 mΩ @ 4.5 V	




N-CHANNEL MOSFET



WDFN8 3.3 x 3.3, 0.65P
CASE 511DH

MARKING DIAGRAM



FDMC86102L = Specific Device Code
A = Assembly Site
L = Wafer Lot Number
YW = Assembly Start Week

ORDERING INFORMATION

Device	Package	Shipping†
FDMC86102L	WDFN8 (Pb-Free, Halide Free)	3000 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, [BRD8011/D](#).

THERMAL CHARACTERISTICS

Symbol	Parameter	Value	Unit
$R_{\theta JC}$	Thermal Resistance, Junction to Case	3	$^{\circ}\text{C}/\text{W}$
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient (Note 1a)	53	

ELECTRICAL CHARACTERISTICS ($T_J = 25^{\circ}\text{C}$ unless otherwise noted)

Symbol	Parameter	Test Condition	Min	Typ	Max	Unit
--------	-----------	----------------	-----	-----	-----	------

OFF CHARACTERISTICS

BV_{DSS}	Drain to Source Breakdown Voltage	$I_D = 250\ \mu\text{A}$, $V_{GS} = 0\ \text{V}$	100	–	–	V
$\Delta BV_{DSS} / \Delta T_J$	Breakdown Voltage Temperature Coefficient	$I_D = 250\ \mu\text{A}$, referenced to 25°C	–	71	–	$\text{mV}/^{\circ}\text{C}$
I_{DSS}	Zero Gate Voltage Drain Current	$V_{DS} = 80\ \text{V}$, $V_{GS} = 0\ \text{V}$	–	–	1	μA
I_{GSS}	Gate to Source Leakage Current	$V_{GS} = \pm 20\ \text{V}$, $V_{DS} = 0\ \text{V}$	–	–	± 100	nA

ON CHARACTERISTICS

$V_{GS(th)}$	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}$, $I_D = 250\ \mu\text{A}$	1	1.8	3	V
$\Delta V_{GS(th)} / \Delta T_J$	Gate to Source Threshold Voltage Temperature Coefficient	$I_D = 250\ \mu\text{A}$, referenced to 25°C	–	–6	–	$\text{mV}/^{\circ}\text{C}$
$R_{DS(on)}$	Static Drain to Source On Resistance	$V_{GS} = 10\ \text{V}$, $I_D = 7\ \text{A}$	–	18.9	23	$\text{m}\Omega$
		$V_{GS} = 4.5\ \text{V}$, $I_D = 5.5\ \text{A}$	–	24.9	34	
		$V_{GS} = 10\ \text{V}$, $I_D = 7\ \text{A}$, $T_J = 125^{\circ}\text{C}$	–	31.9	39	
g_{FS}	Forward Transconductance	$V_{DS} = 5\ \text{V}$, $I_D = 7\ \text{A}$	–	26	–	S

DYNAMIC CHARACTERISTICS

C_{iss}	Input Capacitance	$V_{DS} = 50\ \text{V}$, $V_{GS} = 0\ \text{V}$, $f = 1\ \text{MHz}$	–	999	1330	pF
C_{oss}	Output Capacitance		–	178	240	pF
C_{rss}	Reverse Transfer Capacitance		–	7.6	15	pF
R_g	Gate Resistance		–	0.5	–	Ω

SWITCHING CHARACTERISTICS

$t_{d(on)}$	Turn-On Delay Time	$V_{DD} = 50\ \text{V}$, $I_D = 7\ \text{A}$, $V_{GS} = 10\ \text{V}$, $R_{GEN} = 6\ \Omega$	–	7.7	16	ns
t_r	Rise Time		–	2.2	10	ns
$t_{d(off)}$	Turn-Off Delay Time		–	19	34	ns
t_f	Fall Time		–	2.4	10	ns
$Q_{g(TOT)}$	Total Gate Charge	$V_{GS} = 0\ \text{V}$ to $10\ \text{V}$, $V_{DD} = 50\ \text{V}$, $I_D = 7\ \text{A}$	–	15	22	nC
		$V_{GS} = 0\ \text{V}$ to $4.5\ \text{V}$, $V_{DD} = 50\ \text{V}$, $I_D = 7\ \text{A}$	–	7.3	11	nC
Q_{gs}	Gate to Source Charge	$V_{DD} = 50\ \text{V}$, $I_D = 7\ \text{A}$	–	2.7	–	nC
Q_{gd}	Gate to Drain "Miller" Charge	$V_{DD} = 50\ \text{V}$, $I_D = 7\ \text{A}$	–	2.3	–	nC

FDMC86102L


ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise noted) (continued)

Symbol	Parameter	Test Condition	Min	Typ	Max	Unit
DRAIN-SOURCE DIODE CHARACTERISTICS						
V _{SD}	Source to Drain Diode Forward Voltage	V _{GS} = 0 V, I _S = 7 A (Note 2)	–	0.81	1.3	V
		V _{GS} = 0 V, I _S = 2 A (Note 2)	–	0.74	1.2	
t _{rr}	Reverse Recovery Time	I _F = 7 A, di/dt = 100 A/μs	–	45	72	ns
Q _{rr}	Reverse Recovery Charge		–	45	72	nC


Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

NOTES:

1. R_{θJA} is determined with the device mounted on a 1 in² pad 2 oz copper pad on a 1.5 x 1.5 in. board of FR-4 material. R_{θJC} is guaranteed by design while R_{θCA} is determined by the user's board design.



a) 53°C/W when mounted on a 1 in² pad of 2 oz copper.



b) 125°C/W when mounted on a minimum pad of 2 oz copper.

2. Pulse Test: Pulse Width < 300 μs, Duty cycle < 2.0%.
3. Starting T_J = 25°C; N-ch: L = 1 mH, I_{AS} = 11.3 A, V_{DD} = 90 V, V_{GS} = 10 V.

TYPICAL CHARACTERISTICS


(T_J = 25°C unless otherwise noted)

Figure 1. On-Region Characteristics




Figure 2. Normalized On-Resistance vs. Drain Current and Gate Voltage




Figure 3. Normalized On-Resistance vs. Junction Temperature




Figure 4. On-Resistance vs. Gate to Source Voltage




Figure 5. Transfer Characteristics




Figure 6. Source to Drain Diode Forward Voltage vs. Source Current

TYPICAL CHARACTERISTICS (continued)

($T_J = 25^\circ\text{C}$ unless otherwise noted)




Figure 7. Gate Charge Characteristics




Figure 8. Capacitance vs. Drain to Source Voltage




Figure 9. Unclamped Inductive Switching Capability




Figure 10. Maximum Continuous Drain Current vs. Case Temperature




Figure 11. Forward Bias Safe Operating Area




Figure 12. Single Pulse Maximum Power Dissipation

TYPICAL CHARACTERISTICS (continued)




(T_J = 25°C unless otherwise noted)

Figure 13. Junction-to-Ambient Transient Thermal Response Curve

onsemi[™]

DATE 31 JUL 2016



NOTES:

- A. DOES NOT CONFORM TO JEDEC REGISTRATION MO-229
- B. DIMENSIONS ARE IN MILLIMETERS.
- C. DIMENSIONS AND TOLERANCES PER ASME Y14.5M, 2009.
- D. LAND PATTERN RECOMMENDATION IS EXISTING INDUSTRY LAND PATTERN.

onsemi and **onsemi** are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales