

AX5043-1 DVK2b Module Performance TX



ON Semiconductor®

www.onsemi.com

Introduction

This application note documents output power and transmit currents versus frequency, power settings and VDDIO for the following AX5043 modules:
DVK2b-AX5043-2 V1.3 868 MHz / NB,
DVK2b-AX5043-2 V1.3 433 MHz / NB and
DVK2-AX5043-LF2 V1.2 169 MHz / NB.

APPLICATION NOTE

DVK2b-AX5043-2 V1.3 868 MHz / NB Module

Setup

RF Module	DVK2b-AX5043-2 V1.3 868 MHz / NB with 16MHz TCXO unless stated otherwise. Using the internal VCO.
Main Board	DVK2b, powering the AX5043 via an external power supply
Setup Software	AX-RadioLAB_v2.1f
Software Setup	Basic & Regulatory Tests, Set Pattern, 10kbps GFSK, BT= 0.5. Output Power is varied by changing "Transmit Power" in the PHY panel, which determines the AX5043's TXPWRCOEFFB setting. Output power is plotted against TXPWRCOEFFB, rather than the "transmit power" setting.
RF Measurement equipment	Huber & Suhner 10 dB attenuator directly at the RF Module, 0.5 m Huber & Suhner RG-58 cable to Rhode & Schwarz FSEB spectrum analyzer. Measuring peak power with trace clear / write; RBW = 100 kHz; detector AUTO SELECT, AUTO PEAK; ATTEN AUTO NORMAL Power levels are spectrum analyzer readings plus 11 dB.

Output Power versus Power Setting and VDDIO




Figure 1. Output Power of the Differential and Single Ended PA versus TXPWRCOEFFB Register Setting at 868.3 MHz, VDDIO = 1.8 v and 3.0 V




Figure 2. Output Power of the Differential and Single Ended PA versus VDDIO for TXPWRCOEFFB = 0xFF (Maximum Power) at 868.3 MHz

Transmit Current versus Output Power




Figure 3. Transmit Current versus Output Power of the Differential and Single Ended PA at 868.3 MHz using a 16 MHz TCXO. (TCXO Current not included.) VDDIO = 1.8 V and 3.0 V.

NOTE: This module is optimized for maximum output power. With a matching network optimized for 0 dBm the transmit current at 0 dBm is 8.5 mA, rather than 12 – 15 mA.

AND9314/D

Output Power versus Frequency




Figure 4. Output Power and Transmit Current versus Frequency for TXPWRCOEFFB = 0xFF (Maximum Power) using the Differential PA and a 48 MHz TCXO. (TCXO Current not included.) VDDIO = 3.0 V

DVK2b-AX5043-2 V1.3 433 MHz / NB Module

Setup

RF Module	DVK2b-AX5043-2 V1.3 433 MHz / NB with 16 MHz TCXO unless stated otherwise. Using the internal VCO.
Main Board	DVK2b, powering the AX5043 via an external power supply
Setup Software	AX-RadioLAB_v2.1f
Software Setup	Basic & Regulatory Tests, Set Pattern, 10 kbps GFSK, BT = 0.5. Output Power is varied by changing "Transmit Power" in the PHY panel, which determines the AX5043's TXPWRCOEFFB setting. Output power is plotted against TXPWRCOEFFB, rather than the "transmit power" setting.
RF Measurement equipment	Huber & Suhner 10 dB attenuator directly at the RF Module, 0.5 m Huber & Suhner RG-58 cable to Rhode & Schwarz FSEB spectrum analyzer. Measuring peak power with trace clear / write; RBW = 100 kHz; detector AUTO SELECT, AUTO PEAK; ATTN AUTO NORMAL Power levels are spectrum analyzer readings plus 10.75 dB.

Output Power versus Power Setting and VDDIO




Figure 5. Output Power of the Differential and Single Ended PA versus TXPWRCOEFFB Register Setting at 433.15 MHz, VDDIO = 1.8 V and 3.0 V




Figure 6. Output Power of the Differential and Single Ended PA versus VDDIO for TXPWRCOEFFB = 0xFF (Maximum Power) at 433.15 MHz

Transmit Current versus Output Power




Figure 7. Transmit Current versus Output Power of the Differential and Single Ended PA at 433.15 MHz using a 16 MHz TCXO. (The TCXO Current is not included.)

NOTE: This module is optimized for maximum output power. With a matching network optimized for 0 dBm the transmit current at 0 dBm is 8.5 mA, rather than 12 – 15 mA.

AND9314/D

Output Power versus Frequency




Figure 8. Output Power and Transmit Current versus Frequency for TXPWRCOEFFB = 0xFF (Maximum Power) using the Differential PA and a 48 MHz TCXO. (TCXO Current not included.) VDDIO = 3.0 V

DVK2-AX5043-LF2 V1.2 169 MHz / NB Module

Setup

RF Module	DVK2-AX5043-LF2 V1.2 169 MHz / NB with 16 MHz TCXO unless stated otherwise. Using VCO2 with external L.
Main Board	DVK2b with connectors for DVK2 modules added, powering the AX5043 via an external power supply
Setup Software	AX-RadioLAB_v2.1f
Software Setup	Basic & Regulatory Tests, Set Pattern, 10 kbps GFSK, BT = 0.5. Output Power is varied by changing "Transmit Power" in the PHY panel, which determines the AX5043's TXPWRCOEFFB setting. Output power is plotted against TXPWRCOEFFB, rather than the "transmit power" setting.
RF Measurement equipment	Huber & Suhner 10 dB attenuator directly at the RF Module, 0.5 m Huber & Suhner RG-58 cable to Rhode & Schwarz FSEB spectrum analyzer. Measuring peak power with trace clear / write; RBW = 100 kHz; detector AUTO SELECT, AUTO PEAK; ATTEN AUTO NORMAL Power levels are spectrum analyzer readings plus 10.5 dB.

AND9314/D

Output Power versus Power Setting and VDDIO




Figure 9. Output Power of the Differential and Single Ended PA versus TXPWRCOEFFB Register Setting at 169.3 MHz, VDDIO = 1.8 V and 3.0 V




Figure 10. Output Power of the Differential and Single Ended PA versus VDDIO for TXPWRCOEFFB = 0xFFF (Maximum Power) at 169.3 MHz

Transmit Current versus Output Power




Figure 11. Transmit Current versus Output Power of the Differential and Single Ended PA at 169.3 MHz using a 16 MHz TCXO. (The TCXO Current is not included.)

NOTE: This module is optimized for maximum output power. With a matching network optimized for 0 dBm the transmit current at 0 dBm is 5 mA, rather than 9 – 10 mA.

Output Power versus Frequency




Figure 12. Output Power and Transmit Current versus Frequency for TXPWRCOEFFB = 0xFFFF (Maximum Power) using the Differential PA and a 48 MHz TCXO. (TCXO Current not included.) VDDIO = 3.0 V

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
 Literature Distribution Center for ON Semiconductor
 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free
 USA/Canada
Europe, Middle East and Africa Technical Support:
 Phone: 421 33 790 2910
Japan Customer Focus Center
 Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com
Order Literature: <http://www.onsemi.com/orderlit>
 For additional information, please contact your local
 Sales Representative