ON Semiconductor

Is Now

Onsemi

To learn more about onsemi[™], please visit our website at <u>www.onsemi.com</u>

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product factures, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and asfety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or by customer's technical experts. onsemi products and actal performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiari



ON Semiconductor®

FDMS7694 N-Channel PowerTrench[®] MOSFET 30 V, 9.5 m Ω

Features

- Max $r_{DS(on)}$ = 9.5 m Ω at V_{GS} = 10 V, I_D = 13.2 A
- Max r_{DS(on)} = 14.5 mΩ at V_{GS} = 4.5 V, I_D = 10.5 A
- Advanced Package and Silicon combination for low r_{DS(on)} and high efficiency
- Next generation enhanced body diode technology, engineered for soft recovery
- MSL1 robust package design
- 100% UIL tested
- RoHS Compliant




General Description

This N-Channel MOSFET has been designed specifically to improve the overall efficiency and to minimize switch node ringing of DC/DC converters using either synchronous or conventional switching PWM controllers. It has been optimized for low gate charge, low $r_{DS(on)}$, fast switching speed ang body diode reverse recovery performance.

Applications

- IMVP Vcore Switching for Notebook
- VRM Vcore Switching for Desktop and server
- OringFET / Load Switching
- DC-DC Conversion



Power 56

MOSFET Maximum Ratings $T_A = 25$ °C unless otherwise noted

Symbol	Parameter			Ratings	Units	
V _{DS}	Drain to Source Voltage			30	V	
V _{GS}	Gate to Source Voltage		(Note 4)	±20	V	
ID	Drain Current -Continuous (Package limited)	T _C = 25 °C		20		
	-Continuous (Silicon limited)	T _C = 25 °C		44		
	-Continuous	T _A = 25 °C	(Note 1a)	13.2	A	
	-Pulsed			50		
E _{AS}	Single Pulse Avalanche Energy		(Note 3)	21	mJ	
P _D	Power Dissipation	T _C = 25 °C		27	W	
	Power Dissipation	T _A = 25 °C	(Note 1a)	2.5		
T _J , T _{STG}	Operating and Storage Junction Temperature Range			-55 to +150	°C	

Thermal Characteristics

$R_{ ext{ heta}JC}$	Thermal Resistance, Junction to Case	4.5	°C/W
$R_{ extsf{ heta}JA}$	Thermal Resistance, Junction to Ambient (Note 1	a) 50	C/W

Package Marking and Ordering Information

Device Marking	Device	Package	Reel Size	Tape Width	Quantity
FDMS7694	FDMS7694	Power 56	13 "	12 mm	3000 units

G

s

S

S

4

3


2


1

FDMS7694
N-Channel
PowerTrench [®]
MOSFET

_

Symbol	Parameter	Test Conditions	Min	Тур	Max	Units
Off Chara	octeristics				I	L.
BV _{DSS}	Drain to Source Breakdown Voltage	I _D = 250 μA, V _{GS} = 0 V	30			V
$\frac{\Delta BV_{DSS}}{\Delta T_{J}}$	Breakdown Voltage Temperature Coefficient	$I_D = 250 \ \mu$ A, referenced to 25 °C		16		mV/°C
I _{DSS}	Zero Gate Voltage Drain Current	$V_{DS} = 24 \text{ V}, V_{GS} = 0 \text{ V}$			1	μA
I _{GSS}	Gate to Source Leakage Current, Forward	V _{GS} = 20 V, V _{DS} = 0 V			100	nA
On Chara	cteristics					
V _{GS(th)}	Gate to Source Threshold Voltage	V _{GS} = V _{DS} , I _D = 250 μA	1.0	2.0	3.0	V
$\frac{\Delta V_{GS(th)}}{\Delta T_{.l}}$	Gate to Source Threshold Voltage Temperature Coefficient	$I_D = 250 \ \mu$ A, referenced to 25 °C	-	-6		mV/°C
0	Static Drain to Source On Resistance	V _{GS} = 10 V, I _D = 13.2 A		7.6	9.5	mΩ
r _{DS(on)}		$V_{GS} = 4.5 \text{ V}, \text{ I}_{D} = 10.5 \text{ A}$		11.1	14.5	
		V _{GS} = 10 V, I _D = 13.2 A, T _J = 125 °C		10.6	13.3	
9 _{FS}	Forward Transconductance	V _{DS} = 5 V, I _D = 13.2 A		55		S
Dynamic C _{iss}	Characteristics Input Capacitance			1060	1410	pF
C _{oss}	Output Capacitance	V _{DS} = 15 V, V _{GS} = 0 V, f = 1 MHz		353	470	pF
C _{rss}	Reverse Transfer Capacitance			36	55	pF
R _g	Gate Resistance			0.8	1.6	Ω
Switching	g Characteristics					
t _{d(on)}	Turn-On Delay Time			8.4	17	ns
t _r	Rise Time	V _{DD} = 15 V, I _D = 13.2 A,		2	10	ns
t _{d(off)}	Turn-Off Delay Time	$V_{GS} = 10 \text{ V}, \text{ R}_{GEN} = 6 \Omega$		18	33	ns
t _f	Fall Time			1.6	10	ns
Qg	Total Gate Charge	$V_{GS} = 0 V$ to 10 V		15	22	nC
Qg	Total Gate Charge	$V_{GS} = 0 \text{ V to } 4.5 \text{ V} \text{ V}_{DD} = 15 \text{ V},$		7	10	nC
Q _{gs}	Gate to Source Charge	I _D = 13.2 A		3.3		nC
Q _{gd}	Gate to Drain "Miller" Charge			2.0		nC
Drain-Sou	urce Diode Characteristics					
V	Source to Drain Diode Forward Voltage	$V_{GS} = 0 V, I_S = 2.1 A$ (Note 2)		0.76	1.1	v
V _{SD}		$V_{GS} = 0 V, I_S = 13.2 A$ (Note 2)		0.85	1.2	v
t _{rr}	Reverse Recovery Time	I _F = 13.2 A, di/dt = 100 A/μs		23	37	ns
Q _{rr}	Reverse Recovery Charge			7	14	nC
t _{rr}	Reverse Recovery Time	I _F = 13.2 A, di/dt = 300 A/μs		18	33	ns
Q _{rr}	Reverse Recovery Charge			14	26	nC









b) 125 °C/W when mounted on a minimum pad of 2 oz copper.

00000

2. Pulse Test: Pulse Width < 300 μ s, Duty cycle < 2.0%. 3. E_{AS} of 21 mJ is based on starting T_J = 25 °C, L = 0.3 mH, I_{AS} = 12 A, V_{DD} = 27 V, V_{GS} = 10 V. 100% test at L = 0.1 mH, I_{AS} = 20 A. 4. As an N-ch device, the negative Vgs rating is for low duty cycle pulse occurrence only. No continuous rating is implied.



www.onsemi.com 3




V_{GS}, GATE TO SOURCE VOLTAGE (V)

I_{AS}, AVALANCHE CURRENT (A)

I_D, DRAIN CURRENT (A)

FDMS7694 N-Channel PowerTrench[®] MOSFET



ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor haves, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such uninten

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81–3–5817–1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative