

Is Now Part of



ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at <u>www.onsemi.com</u>

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild_questions@onsemi.com.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or unavteries, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out or i, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor and is officers, employees, uniotificated use, even if such claim any manner.

May 2012

FSTD3125 — 4-Bit Bus Switch with Level Shifting

Features

FAIRCHILD

- 4Ω Switch Connection between Two Ports
- Minimal Propagation Delay through the Switch
- Low I_{CC}
- Zero Bounce in Flow-through Mode
- Control Inputs Compatible with TTL Level
- TruTranslation Voltage Translation from 5.0V Inputs to 3.3V Outputs


Description

Fairchild switch FSTD3125 provides four high-speed CMOS TTL-compatible bus switches. The low on resistance of the switch allows inputs to be connected to outputs without adding propagation delay or generating additional ground bounce noise. A diode to V_{CC} has been integrated into the circuit to allow for level shifting between 5V inputs and 3.3V outputs.

The device is organized as four one-bit switches with separate /OE inputs. When /OE is LOW, the switch is ON and port A is connected to port B. When /OE is HIGH, the switch is OPEN and a high-impedance state exists between the two ports.

Ordering Information

Part Number	Operating Temperature Range	Package	Packing Method
STD3125MTCX	-40 to 85°C	14-Lead, Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 4mm Wide	Tape and Ree
		OE_1 1 A 2 A 2 A 3 OE_2 4 2A 5 OE_3 10 OE_3 10 OE_3 10 OE_3 10 OE_3 10 OE_4 13 OE_4 13 A 12 A 11 A 4B Figure 1. Logic Diagram	R





/OE₁

1A·

1B-

/OE2-

2A-

2B .

GND -

1

2

3

4

5

6

7

Pin Descriptions

Pin Configuration

Pin #	Pin Names	Description
1, 4, 10, 13	/OE ₁ , /OE ₂ , /OE ₃ , /OE ₄	Bus Switch Enables
2, 5, 9, 12	1A, 2A, 3A, 4A	Bus A
3, 6, 8, 11	1B, 2B, 3B, 4B	Bus B
14	V _{cc}	Supply Voltage
7	GND	Ground

Truth Table

Inputs	Inputs/Outputs
/OE	A, B
LOW	A = B
HIGH	High Impedance

Absolute Maximum Ratings

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

Symbol	Parameter	Min.	Max.	Unit
V _{CC}	Supply Voltage	-0.5	7.0	V
Vs	DC Switch Voltage	-0.5	7.0	V
V _{IN}	DC Input Voltage ⁽¹⁾	-0.5	7.0	V
I _{IK}	DC Input Diode Current, V _{IN} <0V		-50	mA
I _{OUT}	DC Output Sink Current		128	mA
I _{CC} / I _{GND}	DC V _{CC} / GND Current		±100	mA
T _{STG}	Storage Temperature Range	-65	+150	°C

Note:

1. The input and output negative voltage ratings may be exceeded if the input and output diode current ratings are observed.

Recommended Operating Conditions

The Recommended Operating Conditions table defines the conditions for actual device operation. Recommended operating conditions are specified to ensure optimal performance to the datasheet specifications. Fairchild does not recommend exceeding them or designing to Absolute Maximum Ratings.

Symbol	Parameter		Min.	Max.	Unit
V _{CC}	Power Supply Operating		4.5	5.5	V
V _{IN}	Input Voltage		0	5.5	V
V _{OUT}	Output Voltage		0	5.5	V
	t Input Diss and Fall Time	Switch Control Input ⁽²⁾	0	5	ns/V
t _r , t _f	Input Rise and Fall Time Switch I/O		0	DC	ns/v
T _A	Operating Temperature, Free Air		-40	+85	°C

Note:

2. Unused control inputs must be held HIGH or LOW. They may not float.

DC Electrical Characteristics

Typical values are at $V_{CC} = 5.0V$ and $T_A = 25^{\circ}C$.

0	Deremeter	Condition		T _A =-40 to +85°C			11
Symbol	Parameter	Condition	V _{cc} (V)	Min.	Тур.	Max.	Unit
V _{IK}	Clamp Diode Voltage	I _{IN} = -18mA	4.5			-1.2	V
VIH	High-Level Input Voltage		4.5 to 5.5	2.0			V
V _{OH}	High-Level	Figure 5, Figure 6, and Figure 7	4.0 to 5.5				V
VIL	Low-Level Input Voltage		4.5 to 5.5			0.8	V
		$0 \le V_{IN} \le 5.5V$	5.5			±1.0	μA
I _{IN}	Input Leakage Current	$V_{IN} = 5.5V$	0			10	μA
I _{OZ}	Off-state Leakage Current	$0 \le A, B \le V_{CC}$	5.5			±1.0	μA
		$V_{IN} = 0V, I_{IN} = 64mA$	4.5		4	7	
R _{ON}	Switch On Resistance ⁽³⁾	$V_{IN} = 0V, I_{IN} = 30mA$	4.5		4	7	Ω
		V _{IN} = 2.4V, I _{IN} = 15mA	4.5		35	50	-
	$/OE_1 = /OE_2 = GND$ $V_{IN} = V_{CC} \text{ or } GND,$ $I_{OUT} = 0$				1.5		
I _{CC} Quiescent Supply Current		$\label{eq:constraint} \begin{split} /OE_1 &= /OE_2 = V_{CC} \\ V_{IN} &= V_{CC} \text{ or GND}, \\ I_{OUT} &= 0 \end{split}$	5.5			10	μA
ΔI_{CC}	Increase in I _{CC} per Input	One Input at 3.4V, Other Inputs at V_{CC} or GND	5.5			2.5	mA

Note:

3. Measured by the voltage drop between the A and B pins at the indicated current through the switch. On resistance is determined by the lower of the voltages on the A or B pins.

AC Electrical Characteristics

 $T_A = -40$ to +85°C, $C_L = 50$ pF, and $R_U = R_D = 500\Omega$.

Symbol	Doromotor	Condition	$V_{\rm CC} = 4.5 - 5.5 V$		Unit	Figure
Symbol	Parameter	Condition	Min. Max.	Unit	Figure	
t _{PHL} , t _{PLH}	Propagation Delay, Bus-to-Bus ⁽⁴⁾	V _{IN} = Open		0.25	ns	Figure 3 Figure 4
t _{PZH} ,t _{PZL}	Output Enable Time	$V_{IN} = 7V$ for t_{PZL} $V_{IN} = Open$ for t_{PZH}	1.0	6.1	ns	Figure 3 Figure 4
t _{PHZ} , t _{PLZ}	Output Disable Time	V_{IN} = 7V for t_{PLZ} V_{IN} = Open for t_{PHZ}	1.5	6.4	ns	Figure 3 Figure 4


Note:

4. This parameter is guaranteed by design, but is not tested. The bus switch contributes no propagation delay other than the RC delay of the typical on resistance of the switch and the 50pF load capacitance when driven by an ideal voltage source (zero output impedance).

Capacitance

 $T_A = +25^{\circ}C$, f = 1MHz. Capacitance is characterized, but not tested.

Symbol	Parameter	Condition	Тур.	Unit
C _{IN}	Control Pin Input Capacitance	$V_{CC} = 5.0V$	3	pF
C _{I/O}	Input/Output Capacitance	V _{CC} , /OE = 5.0V	6	pF



Performance Characteristics






Figure 5. Output Voltage vs. Supply Voltage, V_{IN} = V_{CC}, T_A = 85°C








www.fairchildsemi.com

FSTD3125 — 4-Bit Bus Switch with Level Shifting

6



FAIRCHILD SEMICONDUCTOR TRADEMARKS The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks. 2CoolTh F-PEST PowerTrench[®] The Power Franchise® FRFET® AccuPower™ PowerXS^{TI} wer Global Power ResourceSM Programmable Active Droop™ AX-CAP™* franchise GreenBridge™ BitSiC™ OFET TinyBoost™ QSTM Build it Now™ Green FPS™ TinyBuck™ Green FPS™ e-Series™ Quiet Series™ CorePLUS™ TinyCalc™ RapidConfigure™ CorePOWERTM Gmax™ TinyLogic[®] GTO™)TM **CROSSVOLT™** TINYOPTOT CTL™ IntelliMAX™ Saving our world, 1mW/W/kW at a time™ TinyPower™ Current Transfer Logic™ **ISOPLANAR™** SignalWise™ TinyPWM™ Making Small Speakers Sound Louder DEUXPEED® SmartMax™ TinyWire™ and Better Dual Cool™ SMART START Tran SiC™ EcoSPARK[®] MegaBuckTh Solutions for Your Success™ TriFault Detect™ **MICROCOUPLER™** EfficientMax™ TRUECURRENT®* SPM® **MicroFET™ ESBC™** STEALTH* uSerDes™ MicroPak™ SuperFET® μ MicroPak2™ SuperSOT™-3 Fairchild® Miller Drive™ SuperSOT™-6 Fairchild Semiconductor® UHC Motion Max™ SuperSOT™-8 Ultra FRFET™ FACT Quiet Series™ Motion-SPM™ SupreMOS® UniFET™ FACT mWSaver™ FAST® SyncFET™ **VCX™** OptoHiT™ Sync-Lock™ FastvCore™ VisualMax™ **OPTOLOGIC**[®] **FETBench™** VoltagePlus™ **OPTOPLANAR®** FlashWriter®* XS™ **FPSⁿ** * Trademarks of System General Corporation, used under license by Fairchild Semiconductor.

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used herein:

- Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

ANTI-COUNTERFEITING POLICY

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, www.fairchildsemi.com, under Sales Support.

Counterfeiting of semiconductor parts is a growing problem in the industry. All manufacturers of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed applications, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from Fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handling and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address any warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild to combat this global problem and encourage our customers to obtheir part in stopping this practice by buying direct or from authorized distributors.

PRODUCT STATUS DEFINITIONS

Datasheet Identification	Product Status	Definition
Advance Information	Formative / In Design	Datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design.
No Identification Needed	Full Production	Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.
Obsolete	Not In Production	Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only.

Rev. 161

STD3125

I

4-Bit

Bus

Switch with Level Shifting

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor haves against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death a

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5817-1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

© Semiconductor Components Industries, LLC