

#### Is Now Part of



## ON Semiconductor®

# To learn more about ON Semiconductor, please visit our website at www.onsemi.com

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (\_), the underscore (\_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (\_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at <a href="www.onsemi.com">www.onsemi.com</a>. Please email any questions regarding the system integration to Fairchild <a href="guestions@onsemi.com">guestions@onsemi.com</a>.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officer



March 2015

## **FJP2145**

## **ESBC<sup>™</sup> Rated NPN Power Transistor**

#### **ESBC Features (FDC655 MOSFET)**

V <sub>CS(ON)</sub>	Ic	Equiv. R <sub>CS(ON)</sub> <sup>(1)</sup>
0.21 V	2 A	0.105 Ω

- · Low Equivalent On Resistance
- Very Fast Switch: 150 kHz
- Wide RBSOA: Up to 1100 V
- Avalanche Rated
- · Low Driving Capacitance, No Miller Capacitance
- · Low Switching Losses
- Reliable HV Switch: No False Triggering due to High dv/dt Transients

### **Applications**

- · High-Voltage, High-Speed Power Switch
- Emitter-Switched Bipolar/MOSFET Cascode (ESBC<sup>™</sup>)
- Smart Meters, Smart Breakers, SMPS, HV Industrial Power Supplies
- · Motor Drivers and Ignition Drivers

#### **Description**

The FJP2145 is a low-cost, high-performance power switch designed to provide the best performance when used in an ESBC<sup>™</sup> configuration in applications such as: power supplies, motor drivers, smart grid, or ignition switches. The power switch is designed to operate up to 1100 volts and up to 5 amps, while providing exceptionally low on-resistance and very low switching losses.

The ESBC<sup>™</sup> switch can be driven using off-the-shelf power supply controllers or drivers. The ESBC<sup>™</sup> MOSFET is a low-voltage, low-cost, surface-mount device that combines low-input capacitance and fast switching. The ESBC<sup>™</sup> configuration further minimizes the required driving power because it does not have Miller capacitance.

The FJP2145 provides exceptional reliability and a large operating range due to its square reverse-bias-safe-operating-area (RBSOA) and rugged design. The device is avalanche rated and has no parasitic transistors, so is not prone to static dv/dt failures.

The power switch is manufactured using a dedicated high-voltage bipolar process and is packaged in a high-voltage TO-220 package.



1 BO E O 3




Figure 1. Pin Configuration

Figure 2. Internal Schematic Diagram

Figure 3. ESBC Configuration<sup>(2)</sup>

#### **Ordering Information**

Part Number	Part Number Marking		Packing Method	
FJP2145TU	J2145	TO-220	TUBE	

#### Notes:

- 1. Figure of Merit.
- 2. Other Fairchild MOSFETs can be used in this ESBC application.

#### **Absolute Maximum Ratings**(3)

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only. Values are at  $T_A = 25^{\circ}\text{C}$  unless otherwise noted.

Symbol	Parameter	Value	Unit
V <sub>CBO</sub>	Collector-Base Voltage	1100	V
V <sub>CEO</sub>	Collector-Emitter Voltage	800	V
V <sub>EBO</sub>	Emitter-Base Voltage	7	V
I <sub>C</sub>	Collector Current	5	Α
I <sub>B</sub>	Base Current	1.5	Α
P <sub>C</sub>	Collector Dissipation (T <sub>C</sub> = 25°C)	120	W
TJ	Operating and Junction Temperature Range	-55 to +125	°C
T <sub>STG</sub>	Storage Temperature Range	-55 to +150	°C
EAR <sup>(4)</sup>	Avalanche Energy (T <sub>J</sub> = 25°C, 1.2 mH)	15	mJ

#### Notes:

- 3. Pulse test is pulse width  $\leq$  5 ms, duty cycle  $\leq$  10%.
- 4. Lab characterization data only for reference.

#### **Thermal Characteristics**

Values are at  $T_A = 25$ °C unless otherwise noted.

Symbol	Parameter	Max.	Unit
$R_{\theta jC}$	Thermal Resistance, Junction to Case	1.04	°C/W
$R_{\theta jA}$	Thermal Resistance, Junction to Ambient	78.72	°C/W

## **Electrical Characteristics**(5)

Values are at  $T_A = 25^{\circ}C$  unless otherwise noted.

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
BV <sub>CBO</sub>	Collector-Base Breakdown Voltage	I <sub>C</sub> = 1 mA, I <sub>E</sub> = 0	1100			V
BV <sub>CEO</sub>	Collector-Emitter Breakdown Voltage	$I_C = 5 \text{ mA}, I_B = 0$	800			V
BV <sub>EBO</sub>	Emitter-Base Breakdown Voltage	$I_E = 1 \text{ mA}, I_C = 0$	7			V
I <sub>CBO</sub>	Collector Cut-off Current	$V_{CB} = 800 \text{ V}, I_{E} = 0$			10	μΑ
I <sub>EBO</sub>	Emitter Cut-off Current	$V_{EB} = 5 \text{ V}, I_{C} = 0$			10	μΑ
h <sub>FE1</sub>	DC Current Gain	$V_{CE} = 5 \text{ V}, I_{C} = 0.2 \text{ A}$	20		40	
h <sub>FE2</sub>	DC Current Gain	$V_{CE} = 5 \text{ V}, I_{C} = 1 \text{ A}$	8			
	Collector-Emitter Saturation Voltage	$I_C = 0.25 \text{ A}, I_B = 0.05 \text{ A}$		0.049		V
\/ (cot)		$I_C = 0.5 \text{ A}, I_B = 0.167 \text{ A}$		0.052		V
V <sub>CE</sub> (sat)		I <sub>C</sub> = 1 A, I <sub>B</sub> = 0.33 A		0.082		V
		$I_C = 1.5 \text{ A}, I_B = 0.3 \text{ A}$		0.151	2.000	V
		$I_C = 500 \text{ mA}, I_B = 50 \text{ mA}$		0.752		V
V <sub>BE</sub> (sat)	Base-Emitter Saturation Voltage	$I_C = 1.5 \text{ A}, I_B = 0.3 \text{ A}$		0.833	1.500	V
		I <sub>C</sub> = 2 A, I <sub>B</sub> = 0.4 A		0.855		V
C <sub>IB</sub>	Input Capacitance	$V_{EB} = 5 \text{ V}, I_{C} = 0, f = 1 \text{ MHz}$		1.618		pF
C <sub>OB</sub>	Output Capacitance	$V_{CB} = 200 \text{ V}, I_{E} = 0, f = 1 \text{ MHz}$		11.39		pF
f <sub>T</sub>	Current Gain Bandwidth Product	$V_{CE} = 10 \text{ V}, I_{C} = 0.2 \text{ A}$		15		MHz

#### Note:

5. Pulse test is pulse width ≤ 5 ms, duty cycle ≤ 10%.

## ESBC-Configured Electrical Characteristics(6)

Values are at  $T_A = 25$ °C unless otherwise noted.

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
$f_T$	Current Gain Bandwidth Product	I <sub>C</sub> = 0.1 A,V <sub>CE</sub> = 10 V		28.40		MHz
lt <sub>f</sub>	Inductive Current Fall Time			95		ns
t <sub>s</sub>	Inductive Storage Time	$V_{CC} = 100 \text{ V}, V_{GS} = 10 \text{ V}, R_G = 47\Omega,$		0.13		ns
Vt <sub>f</sub>	Inductive Voltage Fall Time	$V_{Clamp} = 500 \text{ V}, I_{C} = 0.5 \text{ A}, I_{B} = 0.05 \text{ A}, H_{FE} = 10, L_{C} = 166 \mu\text{H},$		135		ns
Vt <sub>r</sub>	Inductive Voltage Rise Time	SRF = 684 kHz		80		ns
t <sub>c</sub>	Inductive Crossover Time			115		ns
lt <sub>f</sub>	Inductive Current Fall Time			50		ns
t <sub>s</sub>	Inductive Storage Time	$V_{CC} = 100 \text{ V}, V_{GS} = 10 \text{ V}, R_G = 47 \Omega,$		0.34		ns
Vt <sub>f</sub>	Inductive Voltage Fall Time	V <sub>Clamp</sub> = 500 V, I <sub>C</sub> = 1 A, I <sub>B</sub> = 0.2 A, H <sub>FF</sub> = 5, L <sub>C</sub> = 166 μH,		150		ns
Vt <sub>r</sub>	Inductive Voltage Rise Time	SRF = 684 kHz		60		ns
t <sub>c</sub>	Inductive Crossover Time			95		ns
V <sub>CSW</sub>	Maximum Collector-Source Voltage at Turn-off without Snubber	h <sub>FE</sub> = 5, I <sub>C</sub> = 2 A	1100			V
I <sub>GS(OS)</sub>	Gate-Source Leakage Current	V <sub>GS</sub> = ± 20 V		1		nA
		$V_{GS} = 10 \text{ V}, I_C = 2 \text{ A}, I_B = 0.67 \text{ A}, h_{FE} = 3$		0.202		V
<b>N</b> /	Collector-Source On	$V_{GS} = 10 \text{ V}, I_C = 1 \text{ A}, I_B = 0.33 \text{ A}, h_{FE} = 3$		0.111		V
V <sub>CS(ON)</sub>	Voltage	$V_{GS} = 10 \text{ V}, I_C = 0.5 \text{ A}, I_B = 0.17 \text{ A}, h_{FE} = 3$		0.067		٧
		$V_{GS} = 10 \text{ V}, I_C = 0.3 \text{ A}, I_B = 0.06 \text{ A}, h_{FE} = 5$		0.060		V
V <sub>GS(th)</sub>	Gate Threshold Voltage	$V_{BS} = V_{GS, I_B} = 250 \mu\text{A}$		1.9		V
C <sub>iss</sub>	Input Capacitance (V <sub>GS</sub> = V <sub>CB</sub> = 0)	V <sub>CS</sub> = 25 V, f = 1 MHz		470		pF
Q <sub>GS(tot)</sub>	Gate-Source Change V <sub>CB</sub> = 0	$V_{GS} = 10 \text{ V}, I_{C} = 6.3 \text{ A}, V_{CS} = 25 \text{ V}$		9		nC
	Static Drain-to-Source On Resistance	V <sub>GS</sub> = 10 V, I <sub>D</sub> = 6.3 A		21		mΩ
R <sub>DS(ON)</sub>		V <sub>GS</sub> = 4.5 V, I <sub>D</sub> = 5.5 A		26		mΩ
, ,		V <sub>GS</sub> = 10 V, I <sub>D</sub> = 6.3 A, T <sub>J</sub> = 125°C		30		mΩ

#### Note:

6. A typical FDC655 MOSFET was used for the specifications above. Values could vary if other Fairchild MOSFETs are used.

### **Typical Performance Characteristics** 100 V<sub>CE</sub> = 5 V I<sub>B</sub> = 1 A Ic [A], COLLECTOR CURRENT 0.9 A h<sub>Fe</sub>, DC CURRENT GAIN 0.7 A 0.6 A 0.5 A 0.4 A 0.3 A 0.1 A 125 °C 25 °C -25 °C 1 └─ 1E-3 0.1 $V_{_{CF}}[V]$ , COLLECTOR-EMITTER VOLTAGE $I_{_{\rm C}}$ [A], COLLECTOR CURRENT Figure 4. Static Characteristics Figure 5. DC Current Gain HFE = 3 V<sub>CE</sub>(sat) [V], SATURATION VOLTAGE Voe (sat) [V], SAT URATION VOLTAGE 0.1 125 °C 125 °C 25 °C -25 °C - 40 °C -40 °C 0.01 └─ 1E-3 $\rm I_{_{\rm C}}$ [A], COLLECTOR CURRENT I<sub>C</sub> [A], COLLECTOR CURRENT Figure 6. Collector-Emitter Saturation Voltage Figure 7. Collector-Emitter Saturation Voltage $h_{FE} = 3$ $h_{FE} = 5$ HFE = 20 HFE = 10 V<sub>CE</sub>(sat) [V], SATURATION VOLTAGE V<sub>CE</sub>(sat) [V], SATURATION VOLTAGE 125 °C 25 °C 125 °C -25 °C -40 °C 25 °C I<sub>c</sub> [A], COLLECTOR CURRENT $I_{_{\rm C}}$ [A], COLLECTOR CURRENT Figure 8. Collector-Emitter Saturation Voltage Figure 9. Collector-Emitter Saturation Voltage $h_{FE} = 10$ h<sub>FE</sub> = 20

## **Typical Performance Characteristics** (Continued)




Figure 10. Typical Collector Saturation Voltage




Figure 12. Inductive Load Collector Current Fall - Time  $(t_{\rm f})$ 




Figure 14. Inductive Load Collector Voltage Fall - Time  $(t_{\rm f})$ 




Figure 11. Capacitance




Figure 13. Inductive Load Collector Current Storage - Time (t<sub>stq</sub>)




Figure 15. Inductive Load Collector Voltage Rise - Time  $(t_r)$ 

## **Typical Performance Characteristics** (Continued)




Figure 16. Inductive Load Collector Current / Voltage Crossover  $(t_c)$ 




Figure 18. ESBC RBSOA




Figure 20. Power Derating




Figure 17. BJT RBSOA




Figure 19. Crossover FBSOA

## **Test Circuits**




Figure 21. Test Circuit For Inductive Load and Reverse Bias Safe Operating




Figure 22. Energy Rating Test Circuit




Figure 23. Ft Measurement

Figure 24. FBSOA

## Test Circuits (Continued)




Figure 25. Simplified Saturated Switch Driver Circuit

## **Functional Test Waveforms**




Figure 26. Crossover Time Measurement




Figure 27. Saturated Switching Waveform

## Functional Test Waveforms (Continued)




Figure 28. Storage Time - Common Emitter Base Turn Off (lb2) to I<sub>C</sub> Fall - Time





Figure 29. Storage Time - ESBC FET Gate (Off) to  $I_{\rm C}$  Fall - Time

## **Very Wide Input Voltage Range Supply**



\* Make short as possible

Figure 30. 30 W; Secondary-Side Regulation: 3 Capacitor Input; Quasi Resonant

## **Driving ESBC Switches**





Figure 31.  $V_{CC}$  Derived

Figure 32. V<sub>BIAS</sub> Supply Derived

Figure 33. Proportional Drive







#### TRADEMARKS

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

 $\begin{array}{lll} \text{BitSiC}^{\intercal M} & \text{Green FPS}^{\intercal M} \\ \text{Build it Now}^{\intercal M} & \text{Green FPS}^{\intercal M} \text{ e-Series}^{\intercal M} \end{array}$ 

Current Transfer Logic™ Making Small Speakers Sound Louder DEUXPEED® and Better™

DUAL COOI™ MegaBuck™

EcoSPARK® MICROCOUPLER™

EfficientMax™ MicroFET™

ESBC™ MicroPak™

Fairchild® MillerDrive™
Fairchild Semiconductor® MotionMax™
FACT Quiet Series™ MTi®
FAST® MTx®
FastvCore™ MVN®
FETBench™ mWSaver®
FPS™ OptoHiT™

OPTOPLANAR®

® PowerTrench® PowerXS™

Programmable Active Droop™

QFET<sup>®</sup>
QS<sup>™</sup>
Quiet Series<sup>™</sup>
RapidConfigure<sup>™</sup>

Saving our world, 1mW/W/kW at a time™

SignalWise™ SmartMax™ SMART START™

Solutions for Your Success™

SPM®
STEALTH™
SuperFET®
SuperSOT™-3
SuperSOT™-6
SuperSOT™-6
SuperSOT™-8
SuperSOT™-8
SuperSOT™-8
SuperSOT™-8
SuperSOT™-8
SuperSOT™-8
SuperSOT™-8
SuperSOT™-8

SYSTEM GENERAL®

TinyBoost®
TinyBuck®
TinyCalc™
TinyLogic®
TiNYOPTO™
TinyPower™
TinyPWM™
TinyWire™
TranSiC™
TFEQUIT Potent

TriFault Detect™
TRUECURRENT®\*
µSerDes™

Serpes\* UHC® Ultra FRFET™ UniFET™ VCX™ VisualMax™ VottagePlus™ XS™ Msens™ Misual™ UniFeT™ Misual™ Mi

\* Trademarks of System General Corporation, used under license by Fairchild Semiconductor.

OPTOLOGIC®

#### DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. TO OBTAIN THE LATEST, MOST UP-TO-DATE DATASHEET AND PRODUCT INFORMATION, VISIT OUR WEBSITE AT <a href="http://www.fairchildsemi.com">http://www.fairchildsemi.com</a>, FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OF CIRCUIT DESCRIBED HEREIN, NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

#### LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

#### As used herein:

- Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

#### ANTI-COUNTERFEITING POLICY

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, www.fairchildsemi.com, under Sales Support

Counterfeiting of semiconductor parts is a growing problem in the industry. All manufacturers of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed applications, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from Fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handling and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address any warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

#### PRODUCT STATUS DEFINITIONS

#### **Definition of Terms**

Datasheet Identification		Definition		
Advance Information	Formative / In Design	Datasheet contains the design specifications for product development. Specifications may change in any manner without notice.		
Preliminary	First Production	Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design.		
No Identification Needed	Full Production	Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.		
Obsolete	Not In Production	Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only.		

Rev. 173

ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdt/Patent-Marking.pdf">www.onsemi.com/site/pdt/Patent-Marking.pdf</a>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and exp

#### **PUBLICATION ORDERING INFORMATION**

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800-282-9855 Toll Free USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative