Buffer with Open Drain Output

The NL17SG07E MiniGate[™] is an advanced high-speed CMOS Buffer with Open Drain Output in ultra-small footprint.

The NL17SG07E input and output structures provide protection when voltages up to 3.6 V are applied regardless of the supply voltage.

Features

- Wide Operating V_{CC} Range: 0.9 V to 3.6 V
- High Speed: $t_{PD} = 2.5$ ns (Typ) at $V_{CC} = 3.0$ V, $C_L = 15$ pF
- Low Power Dissipation: $I_{CC} = 0.5 \mu A$ (Max) at $T_A = 25^{\circ}C$
- 3.6 V Overvoltage Tolerant (OVT) Input and Output Pins
- Ultra-Small Packages
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant




Figure 1. SC-88A (Top View)



Figure 2. Logic Symbol



ON Semiconductor®

www.onsemi.com





SC-88A DF SUFFIX CASE 419A



MARKING

M = Date Code*

= Pb–Free Package

(Note: Microdot may be in either location)

*Date Code orientation and/or position may vary depending upon manufacturing location.

PIN ASSIGNMENT

PIN	NAME
1	NC
2	А
3	GND
4	Y
5	V _{CC}

FUNCTION TABLE

Input A	Output Y
L	L
Н	Z

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 5 of this data sheet.

MAXIMUM RATINGS

Symbol	Parameter	Value	Unit
V_{CC}	DC Supply Voltage	-0.5 to +4.6	V
V _{IN}	DC Input Voltage	-0.5 to +4.6	V
V _{OUT}	DC Output Voltage Active Mode, LOW State Tri–State Mode, Output at Hi–Z State Power–Down Mode (V_{CC} = 0 V)	-0.5 to V _{CC} + 0.5 -0.5 to +4.6 -0.5 to +4.6	V
I _{IK}	DC Input Diode Current V _{IN} < GND	-20	mA
I _{OK}	DC Output Diode Current V _{OUT} < GND	-20	mA
I _{OUT}	DC Output Source/Sink Current	±20	mA
I _{CC}	DC Supply Current per Supply Pin	±20	mA
I _{GND}	DC Ground Current per Ground Pin	±20	mA
T _{STG}	Storage Temperature Range	-65 to +150	°C
TL	Lead Temperature, 1 mm from Case for 10 Seconds	260	°C
TJ	Junction Temperature Under Bias	+150	°C
MSL	Moisture Sensitivity	Level 1	
F _R	Flammability Rating Oxygen Index: 28 to 34	UL 94 V-0 @ 0.125 in	
V _{ESD}	ESD Withstand Voltage Human Body Model (Note 2)	>2000	V
I _{LATCHUP}	Latch-up Performance above V _{CC} and below GND at 125°C (Note 3)	±75	mA

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

- Measured with minimum pad spacing on an FR4 board, using 10 mm-by-1 inch, 2-ounce copper trace with no air flow.
 Tested to EIA/JESD22-A114-A.
- 3. Tested to EIA/JESD78.

RECOMMENDED OPERATING CONDITIONS

Symbol	Char	Min	Max	Unit	
V _{CC}	Positive DC Supply Voltage		0.9	3.6	V
V_{IN}	Digital Input Voltage		0.0	3.6	V
V _{OUT}	Output Voltage	Output at Low State Tri–State Mode, Output at Hi–Z State Power–Down Mode ($V_{\rm CC}$ = 0 V)	0.0 0.0 0.0	V _{CC} 3.6 3.6	V
T _A	Operating Temperature Range		-55	+125	°C
Δt / ΔV	Input Transition Rise or Fail Rate	V_{CC} = 3.3 V \pm 0.3 V	0	10	ns/V

Functional operation above the stresses listed in the Recommended Operating Ranges is not implied. Extended exposure to stresses beyond the Recommended Operating Ranges limits may affect device reliability.

DC ELECTRICAL CHARACTERISTICS

				V _{CC}		T _A = 25°C	;	-55°C ≤ 1	Γ _A ≤ 125°C	
Symbol	Parameter	С	ondition	(V)	Min	Тур	Max	Min	Max	Unit
V_{IH}	High-Level			0.9	V _{CC}			V _{CC}		
	Input Voltage			1.1 to 1.3	0.70 x V _{CC}			0.70 x V _{CC}		
				1.4 to 1.6	0.65 x V _{CC}			0.65 x V _{CC}		V
				1.65 to 1.95	0.65 x V _{CC}			0.65 x V _{CC}		
				2.3 to 2.7	1.7			1.7		
				3.0 to 3.6	2.0			2.0		
V _{IL}	Low-Level			0.9			GND		GND	
	Input Voltage			1.1 to 1.3			0.30 x V _{CC}		0.30 x V _{CC}	
				1.4 to 1.6			0.35 x V _{CC}		0.35 x V _{CC}	V
				1.65 to 1.95			0.35 x V _{CC}		0.35 x V _{CC}	
				2.3 to 2.7			0.7		0.7	1
				3.0 to 3.6			0.8		0.8	
V _{OL}	Low-Level	V _{IN} =	I _{OL} = 20 μA	0.9			0.1		0.1	V
	Output Voltage	V _{IH} or V _{IL}	I _{OL} = 0.3 mA	1.1 to 1.3			0.25 x V _{CC}		0.25 x V _{CC}	
			I _{OL} = 1.7 mA	1.4 to 1.6			0.25 x V _{CC}		0.25 x V _{CC}	
			I _{OL} = 3.0 mA	1.65 to 1.95			0.45		0.45	
			I _{OL} = 4.0 mA	2.3 to 2.7			0.4		0.4	-
			$I_{OL} = 8.0 \text{ mA}$	3.0 to 3.6			0.4		0.4	
I _{IN}	Input Leakage Current	V _{IN}	= 0 to 3.6 V	0.9 to 3.6			±0.1		±1.0	μΑ
I _{CC}	Quiescent Supply Current	V _{IN} =	V _{CC} or GND	3.6			0.5		10	μΑ
l _{OZ}	Output Tri– State Leakage Current	V _{IN} : V _{OUT}	= V_{IH} or V_{IL} , = 0 to 3.6 V	0.9 to 3.6			1.0		10	μΑ
l _{OFF}	Power Off Leakage Cur- rent	V _{IN} V _{OUT}	= 0 to 3.6 V = 0 to 3.6 V	0			1.0		10	μΑ

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

AC ELECTRICAL CHARACTERISTICS (Input $t_r = t_f = 3.0 \text{ ns}$)

					T _A = 25°C	;	T⊿ –55°C to	. = o +125°C	
Symbol	Parameter	Test Condition	V _{CC} (V)	Min	Тур	Max	Min	Max	Uni
t _{PZL}	Propagation Delay,	$C_L = 10 pF$,	0.9	-	12	_	-	-	ns
	Enable Time,	$R_1 = R_L = 5 \text{ k}\Omega$	1.1 to 1.3	_	5.5	7.9	-	9.0	
	A to Y		1.4 to 1.6	_	4.0	5.7	-	7.3	
			1.65 to 1.95	_	3.3	3.9	_	5.9	1
			2.3 to 2.7	_	2.7	3.3	_	4.5	1
			3.0 to 3.6	-	2.4	2.9	-	3.7	
		$C_L = 15 pF$,	0.9	-	12.5	_	-	-	ns
		$R_1 = R_L = 5 \text{ k}\Omega$	1.1 to 1.3	-	5.8	8.1	-	9.2	
			1.4 to 1.6	-	4.1	6.0	-	7.4	
			1.65 to 1.95	_	3.4	4.0	_	6.2	1
			2.3 to 2.7	_	2.8	3.4	_	4.6	1
			3.0 to 3.6	-	2.5	3.0	_	3.7	1
		C _L = 30 pF,	0.9	_	13.2	_	_	-	n
		$R_1 = R_L = 5 \text{ k}\Omega$	1.1 to 1.3	-	6.2	8.7	_	9.8	
			1.4 to 1.6	-	4.5	6.2	_	7.6	
			1.65 to 1.95	-	3.5	4.2	_	6.4	
			2.3 to 2.7	-	3.0	3.6	_	4.7	
			3.0 to 3.6	-	2.6	3.1	_	3.9	
t _{PLZ}	Propagation Delay,	$C_L = 10 \text{ pF},$	0.9	_	8.0	-	-	-	ns
	Disable Time,	$R_1 = R_L = 5 \text{ k}\Omega$	1.1 to 1.3	-	6.5	10.9	-	11.5	
	A to Y		1.4 to 1.6	-	5.2	8.9	-	9.5	
			1.65 to 1.95	-	4.9	8.8	-	9.4	
			2.3 to 2.7	-	3.8	8.4	-	9.3	
			3.0 to 3.6	-	3.5	8.1	-	8.5	
		C _L = 15 pF,	0.9	-	11.1	_	-	-	n
		$R_1 = R_L = 5 \text{ k}\Omega$	1.1 to 1.3	-	9.0	13.4	-	14	
			1.4 to 1.6	-	7.9	11.4	-	12.0	
			1.65 to 1.95	-	7.6	11.3	-	11.9	
			2.3 to 2.7	-	6.3	10.9	-	11.8	
			3.0 to 3.6	-	6.0	10.6	-	11.0	
		$C_L = 30 \text{ pF},$ $R_1 = R_L = 5 \text{ k}\Omega$	0.9	-	16.2	-	-	-	n
		$R_1 = R_L = 5 \text{ k}\Omega$	1.1 to 1.3	-	14	20.2	-	20	1
			1.4 to 1.6	-	13	18.9	-	19.5	1
			1.65 to 1.95	-	12.5	18.8	-	19.4	1
			2.3 to 2.7	_	11.2	18.4	-	19.3	1
			3.0 to 3.6	_	11	18.1	-	18.3	-
C _{IN}	Input Capacitance		0 to 3.6	_	3	_	_	-	pl
C _{PD}	Power Dissipation Capacitance (Note 4)		0.9 to 3.6	-	4	_	_	-	pl

^{4.} C_{PD} is defined as the value of the internal equivalent capacitance which is calculated from the dynamic operating current consumption without load. Average operating current can be obtained by the equation: I_{CC(OPR)} = C_{PD} • V_{CC} • f_{in} + I_{CC}. C_{PD} is used to determine the no–load dynamic power consumption; P_D = C_{PD} • V_{CC}² • f_{in} + I_{CC} • V_{CC}.




Figure 3. Switching Waveform




Figure 4. Test Circuit

ORDERING INFORMATION

Device	Package	Shipping [†]
NL17SG07EDFT2G	SC-88A (Pb-Free)	3000 / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.





SC-88A (SC-70-5/SOT-353) CASE 419A-02 ISSUE M


DATE 11 APR 2023

NOTES:


- 1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
- 2. CONTROLLING DIMENSION: MILLIMETERS
- 3. 419A-01 DBSOLETE, NEW STANDARD 419A-02
- 4. DIMENSIONS D AND E1 DO NOT INCLUDE MOLD FLASH,
 PROTRUSIONS, OR GATE BURRS.MOLD FLASH, PROTRUSIONS,
 OR GATE BURRS SHALL NOT EXCEED 0.1016MM PER SIDE.


DIM	MILLIMETERS				
ابالط	MIN.	MIN. N□M.			
Α	0.80	0.95	1.10		
A1			0.10		
A3	0,20 REF				
b	0.10	0.20	0.30		
С	0.10		0.25		
D	1.80	2.00	2.20		
Е	2.00	2.10	2.20		
E1	1.15	1.25	1.35		
е		0.65 BS	C		
L	0.10	0.15	0.30		

5 + E1 E1 -5X b



◆ 0.2 M B M





RECOMMENDED MOUNTING FOOTPRINT

For additional information on our Pb-Free strategy and soldering details, please download the DN Semiconductor Soldering and Mounting Techniques Reference Manual, SDLDERRM/D.

GENERIC MARKING DIAGRAM*



*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "•", may or may not be present. Some products may not follow the Generic Marking.

XXX = Specific Device Code

M = Date Code

= Pb-Free Package

(Note: Microdot may be in either location)

STYLE 1:
PIN 1. BASE
EMITTER
3. BASE
COLLECTOR
COLLECTOR

STYLE 2:
PIN 1. ANODE
2. EMITTER
3. BASE
4. COLLECTOR
5. CATHODE

STYLE 3: PIN 1. ANODE 1 2. N/C 3. ANODE 2 4. CATHODE 2 5. CATHODE 1 STYLE 4:
PIN 1. SOURCE 1
2. DRAIN 1/2
3. SOURCE 1
4. GATE 1
5. GATE 2

STYLE 5:
PIN 1. CATHODE
2. COMMON ANODE
3. CATHODE 2
4. CATHODE 3
5. CATHODE 4

STYLE 6: PIN 1. EMITTER 2 2. BASE 2 3. EMITTER 1 4. COLLECTOR STYLE 7:
PIN 1. BASE
2. EMITTER
3. BASE
4. COLLECTOR
5. COLLECTOR

STYLE 8:
PIN 1. CATHODE
2. COLLECTOR
3. N/C
4. BASE
5. EMITTER

STYLE 9: PIN 1. ANODE 2. CATHODE 3. ANODE 4. ANODE 5. ANODE Note: Please refer to datasheet for style callout. If style type is not called out in the datasheet refer to the device datasheet pinout or pin assignment.

DOCUMENT NUMBER:

98ASB42984B

Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.

DESCRIPTION:

5. COLLECTOR 2/BASE 1

SC-88A (SC-70-5/SOT-353)

PAGE 1 OF 1

onsemi and ONSEMI are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, Onsemi, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA class 3 medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

 $\textbf{Technical Library:} \ \underline{www.onsemi.com/design/resources/technical-documentation}$

onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at

www.onsemi.com/support/sales