# **ON Semiconductor**

## Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,

# **N-Channel Power MOSFET** 100 V, 77 A, 14 m $\Omega$

### Features

- Low R<sub>DS(on)</sub>
- High Current Capability
- 100% Avalanche Tested
- These are Pb-Free Devices

### MAXIMUM RATINGS (T<sub>J</sub> = 25°C Unless otherwise specified)

Para	Symbol	Value	Unit		
Drain-to-Source Voltage			$V_{DSS}$	100	V
Gate-to-Source Voltage	ge – Conti	nuous	V <sub>GS</sub>	± 20	V
Continuous Drain	,		I <sub>D</sub>	77	Α
Current R <sub>θJC</sub>	State	T <sub>C</sub> = 100°C		54	
Power Dissipation $R_{\theta JC}$	Steady T <sub>C</sub> = 25°C		P <sub>D</sub>	217	W
Pulsed Drain Current	tp	= 10 μs	I <sub>DM</sub>	285	Α
Operating Junction and Storage Temperature Range			T <sub>J</sub> , T <sub>stg</sub>	-55 to +175	°C
Source Current (Body Diode)			I <sub>S</sub>	77	Α
Single Pulse Drain-to-Source Avalanche Energy ( $V_{DD}$ = 50 Vdc, $V_{GS}$ = 10 Vdc, $I_{L(pk)}$ = 56 A, L = 0.3 mH, $R_{G}$ = 25 $\Omega$ )			E <sub>AS</sub>	470	mJ
Lead Temperature for Soldering Purposes, 1/8" from Case for 10 Seconds			TL	260	°C

#### THERMAL RESISTANCE RATINGS

Parameter	Symbol	Max	Unit
Junction-to-Case (Drain) Steady State	$R_{\theta JC}$	0.69	°C/W
Junction-to-Ambient (Note 1)	$R_{\theta JA}$	33	

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

1. Surface mounted on FR4 board using 1 sq in pad size,


(Cu Area 1.127 sq in [2 oz] including traces).




#### ON Semiconductor®


#### http://onsemi.com

V <sub>(BR)DSS</sub>	R <sub>DS(ON)</sub> MAX	I <sub>D</sub> MAX (Note 1)
100 V	14 mΩ @ 10 V	77 A










### **ORDERING INFORMATION**

See detailed ordering and shipping information in the package dimensions section on page 5 of this data sheet.

### **ELECTRICAL CHARACTERISTICS** (T<sub>J</sub> = 25°C Unless otherwise specified)

Characteristics	Symbol	Test Condition		Min	Тур	Max	Unit
OFF CHARACTERISTICS	•	•		_	•	•	
Drain-to-Source Breakdown Voltage	V <sub>(BR)DSS</sub>	$V_{GS} = 0 \text{ V}, I_D = 250 \mu\text{A}$		100			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V <sub>(BR)DSS</sub> /T <sub>J</sub>				113		mV/°C
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	V <sub>GS</sub> = 0 V,	T <sub>J</sub> = 25°C			1.0	μΑ
		V <sub>DS</sub> = 100 V	T <sub>J</sub> = 125°C			100	
Gate-to-Source Leakage Current	I <sub>GSS</sub>	V <sub>DS</sub> = 0 V, V	' <sub>GS</sub> = ±20 V			±100	nA
ON CHARACTERISTICS (Note 2)							
Gate Threshold Voltage	V <sub>GS(th)</sub>	$V_{GS} = V_{DS}$	I <sub>D</sub> = 250 μA	2.0		4.0	V
Negative Threshold Temperature Coefficient	V <sub>GS(th)</sub> /T <sub>J</sub>				8.6		mV/°C
Drain-to-Source On-Resistance	R <sub>DS(on)</sub>	V <sub>GS</sub> = 10 \	/, I <sub>D</sub> = 72 A		12.7	14	mΩ
Forward Transconductance	9FS	V <sub>DS</sub> = 5 V	, I <sub>D</sub> = 10 A		24		S
CHARGES, CAPACITANCES & GATE RESISTA	ANCE				•	•	•
Input Capacitance	C <sub>iss</sub>				3700		pF
Output Capacitance	C <sub>oss</sub>	V <sub>DS</sub> = 25 V f = 1	, V <sub>GS</sub> = 0 V, MHz		550		1
Reverse Transfer Capacitance	C <sub>rss</sub>	'-'	IVII IZ		200		
Total Gate Charge	Q <sub>G(TOT)</sub>				100		nC
Threshold Gate Charge	Q <sub>G(TH)</sub>				4.0		
Gate-to-Source Charge	Q <sub>GS</sub>	$V_{GS} = 10 \text{ V}, V_{DS} = 80 \text{ V},$ $I_{D} = 72 \text{ A}$		,	16		1
Gate-to-Drain Charge	$Q_{GD}$				47		
Plateau Voltage	$V_{GP}$				5.2		V
Gate Resistance	R <sub>G</sub>				3.1		Ω
SWITCHING CHARACTERISTICS, V <sub>GS</sub> = 10 V	(Note 3)					•	•
Turn-On Delay Time	t <sub>d(on)</sub>				16		ns
Rise Time	t <sub>r</sub>	V <sub>GS</sub> = 10 V,	V <sub>DD</sub> = 80 V.		144		7
Turn-Off Delay Time	t <sub>d(off)</sub>	$I_{\rm D} = 72  \rm A,$	$R_G = 6.2 \Omega$		107		1
Fall Time	t <sub>f</sub>	1		,	157		1
DRAIN-SOURCE DIODE CHARACTERISTICS	•	•					
Forward Diode Voltage	V <sub>SD</sub>	I <sub>S</sub> = 72 A	T <sub>J</sub> = 25°C		0.92	1.3	V
			T <sub>J</sub> = 125°C		0.86		
Reverse Recovery Time	t <sub>rr</sub>	V <sub>GS</sub> = 0 V, I <sub>S</sub> = 72 A, dI <sub>S</sub> /dt = 100 A/μs			94		ns
Charge Time	t <sub>a</sub>				64		1
Discharge Time	t <sub>b</sub>				30		1
Reverse Recovery Charge	Q <sub>RR</sub>				330		nC

Pulse Test: Pulse Width ≤ 300 μs, Duty Cycle ≤ 2%.
 Switching characteristics are independent of operating junction temperatures.






Figure 7. Capacitance Variation

Figure 8. Gate-to-Source Voltage and Drain-to-Source Voltage versus Total Charge




Figure 9. Resistive Switching Time Variation versus Gate Resistance




Figure 10. Diode Forward Voltage versus Current




Figure 11. Maximum Rated Forward Biased Safe Operating Area




Figure 12. Maximum Avalanche Energy versus **Starting Junction Temperature** 




Figure 13. Thermal Response


### **ORDERING INFORMATION**

Device	Package	Shipping <sup>†</sup>
NTB6411ANG	D <sup>2</sup> PAK (Pb-Free)	50 Units / Rail
NTB6411ANT4G	D <sup>2</sup> PAK (Pb-Free)	800 / Tape & Reel
NTP6411ANG	TO-220 (Pb-Free)	50 Units / Rail

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

### PACKAGE DIMENSIONS

### D<sup>2</sup>PAK 3 CASE 418B-04 ISSUE K




#### NOTES:


- NOTES:
  1. DIMENSIONING AND TOLERANCING
  PER ANSI Y14.5M, 1982.
  2. CONTROLLING DIMENSION: INCH.
  3. 418B-01 THRU 418B-03 OBSOLETE,
  NEW STANDARD 418B-04.

	INCHES		MILLIMETERS		
DIM	MIN	MAX	MIN	MAX	
Α	0.340	0.380	8.64	9.65	
В	0.380	0.405	9.65	10.29	
С	0.160	0.190	4.06	4.83	
D	0.020	0.035	0.51	0.89	
E	0.045	0.055	1.14	1.40	
F	0.310	0.350	7.87	8.89	
G	0.100	BSC	2.54 BSC		
Н	0.080	0.110	2.03	2.79	
J	0.018	0.025	0.46	0.64	
K	0.090	0.110	2.29	2.79	
L	0.052	0.072	1.32	1.83	
M	0.280	0.320	7.11	8.13	
N	0.197	REF	5.00 REF		
Р	0.079 REF		2.00 REF		
R	0.039	0.039 REF		REF	
S	0.575	0.625	14.60	15.88	
V	0.045	0.055	1.14	1.40	

2. DRAIN 3. SOURCE 4. DRAIN




### **SOLDERING FOOTPRINT\***




\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

#### PACKAGE DIMENSIONS

TO-220 CASE 221A-09 **ISSUE AF** 





#### NOTES:

- DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
- CONTROLLING DIMENSION: INCH.
  DIMENSION Z DEFINES A ZONE WHERE ALL BODY AND LEAD IRREGULARITIES ARE ALLOWED.

	INCHES		MILLIMETERS		
DIM	MIN	MAX	MIN	MAX	
Α	0.570	0.620	14.48	15.75	
В	0.380	0.405	9.66	10.28	
С	0.160	0.190	4.07	4.82	
D	0.025	0.035	0.64	0.88	
F	0.142	0.161	3.61	4.09	
G	0.095	0.105	2.42	2.66	
Н	0.110	0.155	2.80	3.93	
J	0.014	0.025	0.36	0.64	
K	0.500	0.562	12.70	14.27	
L	0.045	0.060	1.15	1.52	
N	0.190	0.210	4.83	5.33	
Q	0.100	0.120	2.54	3.04	
R	0.080	0.110	2.04	2.79	
S	0.045	0.055	1.15	1.39	
T	0.235	0.255	5.97	6.47	
U	0.000	0.050	0.00	1.27	
٧	0.045		1.15		
Z		0.080		2.04	

#### STYLE 5:

- PIN 1. GATE 2 DRAIN
  - SOURCE
  - DRAIN

ON Semiconductor and un are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice on semiconductor and are registered radiations of semiconduction Components industries, Ite (SCILLO). Solitude services are injust of make drainges without further induce to any products herein. SCILLO makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### **PUBLICATION ORDERING INFORMATION**

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada

Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5773-3850

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative